

Enhance your Panel PC solution with integrated OMRON applications




NYSE Embedded Panel PC

The NYE industrial Panel PC offers customers the flexibility to choose the most suitable application solution for their needs. From a Windows-only version with the freedom to install preferred applications to versions that add OMRON software packages for vision systems, 2D code reading or HMI functionality, NYE is designed with durable hardware and software components for long-term use, using high-quality components and innovative mechanical design, and is made to OMRON's highest production standards.



HMI



NYSE Soft-NA

Soft NA allows users to run NA5 HMI applications on an NYE Panel PC. Soft-NA software displays information on FA manufacturing sites while providing a safe, reliable, and easy to maintain industrial display for performing operations as needed.

Vision



NYSE FHV7

FHV7 Software is a software tool for setting up OMRON FHV7 vision systems. Combine image processing applications with data gathering for sophisticated image inspection and data collection using high-speed, high-accuracy inspections and measurement. The FHV7-series Smart Camera combines illumination and image processing functionality for advanced vision inspections.

Windows 10 IoT Enterprise 2021 LTSC



Edge Applications

Control your industrial application from anywhere with any type of Edge device thanks to the Edge controller installed on your OMRON IPC.

Cyber-Security

OMRON continues to work to add secure design processes and product certification. In addition, our IPC opens the possibility of installing packages from the Cybersecurity market.



Code reader




NYE OCR viewer

Component and product traceability are common requirements for today's busy factories and assembly plants. OMRON 2D code readers feature cutting edge technology for decoding 2D symbols and linear barcodes based on OMRON's proven image processing and decoding algorithm development, offering unrivalled performance for reliably decoding challenging codes and direct part marks (DPM).

NYE Platform

Product name	Industrial PC		
Type	Industrial Panel PC		
Model	NYE2A-20511-□	NYE2A-20F11-□	NYE2A-20N11-□
Description	Combines the functionality of the Industrial Box PC and Industrial Monitor		
Operating system	Windows 10 IoT Enterprise 2021 LTSC - 64 bit		
OMRON apps	—	FHV7 Software	Soft NA Software
CPU type	Intel Atom® x5-E3940		
RAM memory	DDR3L 4 GB no ECC		
Storage	128 GB, CFast 3DTLC		
Display size	12.1 inches, 15.4 inches		7.0 inches, 9.0 inches, 12.1 inches, 15.4 inches
Built-in ports	RS-232C, 2 x RJ45 Gb Ethernet interface connectors 10BASE-T/100BASE-TX/1000BASE-T. 2 x USB 2.0 interface connectors 1 x USB 3.0		

Datasheet



The datasheet includes the specifications for the Industrial PC Platform NYE.
For more details, refer to Omron's regional websites.

- Windows is either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.
- Intel, Atom are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries.
- CFast is a registered trademark of CompactFlash Association.
- Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.
- Microsoft product screen shot(s) used with permission from Microsoft.
- The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.
Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands
Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.
438B Alexandra Road, #08-01/02 Alexandra
Technopark, Singapore 119968
Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC
2895 Greenspoint Parkway, Suite 200
Hoffman Estates, IL 60169 U.S.A.
Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.
Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2025 All Rights Reserved.
In the interest of product improvement,
specifications are subject to change without notice.

CSM_1_2
Cat. No. P170-E1-02 1225 (0725)