

Dual-colour panel indicators

K3MA SERIES

excellent visibility and precise read-out


Advanced Industrial Automation


COLOUR CHANGE DISPLAY



 Process

 Temperature







 Frequency & Rate

Actual size: 1/8 DIN (96x48 mm)

Clear precise information on process, temperature and frequency/rate applications.

- High tech back-lit LCD display** *Ensures excellent visibility at all times*
- Large LCD characters** *Ensure excellent visibility over long distances and from wide viewing angles*
- Dual-colour display** *Provides intuitive visible feedback of value status*
- Simple-to-use menu structure** *Gives programming continuity across all applications*
- Easily configurable outputs** *For upper, lower and window limit settings and combinations*
- Scalability** *Enables you to configure values to your requirements*
- Dust-proof and waterproof casing (Nema4X – IP66)** *For top performance in all conditions*
- All models conform to the latest safety standards** *Your world-wide partner for indicators*

OMRON



COLOUR CHANGE DISPLAY

VA Process signals

The K3MA-J indicator accepts all standard process signals, including input currents (0 to 20mA; 4 to 20mA) and input voltages (from 0 to 5V; 1 to 5V; $\pm 5V$ and $\pm 10V$).

- Maximum display digits: -19999 to 99999
- Output Relay: 2SPST-NO
- Additional features: Scaling, Teaching, Forced-zero, Zero-limit functions

Immediately available:

- K3MA-J-A2 100-240 VAC
- K3MA-J-A2 24 VAC/VDC

Application areas:

- Tank pressure monitoring
- Level display
- Flow rate sensor display
- Humidity display

°C Temperature signals

The K3MA-L indicator handles multiple inputs, including two types of platinum-resistance thermometers (Pt100, JPt100) and ten types of thermocouples (K, J, T, E, L, U, N, R, S, B).

- Accuracy: $\pm 0.5\%$ of indicated value
- Maximum display digits: -1999 to 9999
- Output Relay: 1SPDT
- Features: Temperature input shift

Immediately available:

- K3MA-L-C 100-240 VAC
- K3MA-L-C 24 VAC/VDC

Application areas:

- Bearing temperature monitoring
- Plastic moulding temperature control
- Industrial furnace monitoring
- Freeze indicator

Frequency/Rate signals

The K3MA-F indicator accepts multiple inputs connected as standard voltage pulse inputs, NPN/PNP (5 kHz) or contact inputs (30 Hz).

- Sensor supply: 40mA at 12 VDC
- Maximum display digits: -19999 to 99999
- Output Relays: 2SPST-NO
- Additional features: Scaling, Teaching, Auto-zero time, Start-up time

Immediately available:

- K3MA-F-A2 100-240 VAC
- K3MA-F-A2 24 VAC/VDC

Application areas:

- Motor speed
- Axe-rotation speed
- Conveyor belt feed speed
- Low rate display

OMRON EUROPE B.V. Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. Tel: +31 (0) 23 568 13 00 Fax: +31 (0) 23 568 13 88 www.europe.omron.com

Austria
Tel: +43 (0) 1 80 19 00
www.omron.at

Belgium
Tel: +32 (0) 2 466 24 80
www.omron.be

Czech Republic
Tel: +420 267 31 12 54
www.omron.cz

Denmark
Tel: +45 43 44 00 11
www.omron.dk

Finland
Tel: +358 (0) 9 549 58 00
www.omron.fi

France
Tel: +33 (0) 1 49 74 70 00
www.omron.fr

Germany
Tel: +49 (0) 2173 680 00
www.omron.de

Hungary
Tel: +36 (0) 1 399 30 50
www.omron.hu

Italy
Tel: +39 02 32 68 1
www.omron.it

Netherlands
Tel: +31 (0) 23 568 11 00
www.omron.nl

Norway
Tel: +47 (0) 22 65 75 00
www.omron.no

Poland
Tel: +48 (0) 22 645 78 60
www.omron.com.pl

Portugal
Tel: +351 21 942 94 00
www.omron.pt

Russia
Tel: +7 095 745 26 64
www.russia.omron.com

Spain
Tel: +34 913 777 900
www.omron.es

Sweden
Tel: +46 (0) 8 632 35 00
www.omron.se

Switzerland
Tel: +41 (0) 41 748 13 13
www.omron.ch

Turkey
Tel: +90 (0) 216 474 00 40
www.omron.com.tr

United Kingdom
Tel: +44 (0) 870 752 08 61
www.omron.co.uk

For the Middle East, Africa and other countries in Eastern Europe, Tel: +31 (0) 23 568 13 00 www.europe.omron.com

OMRON