Solid State Relays G3 -VD

Solid State Relays Featuring the Same Profile as MY Power Relays

- Reduces wiring work by 60% when combined with the PFY-08-PU Push-In Plus Socket (according to actual OMRON measurements).
- Shape-compatible with mechanical relays.
- Certified by UL, CSA, and VDE.
- Socket type, same size as MY Power Relays.
- Operation indicator provided to confirm input (model numbers with "N" before the suffix).

Refer to Safety Precautions for All Solid State Relays and Safety Precautions on page 7.




Note: The socket is optional.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Structure

Model Number Legend

G3F-_____



- 1. Basic Model Name
- G3F: Solid State Relay
- 2. Rated Load Power Supply Voltage 2: 200 VAC
- 3. Rated Load Current 02: 2 A
 - 03: 3 A
- 4. Terminal Type
- S: Plug-in terminals

5. Zero Cross Function

- Blank: Equipped with zero cross functions
- L: Not equipped with zero cross function
- 6. Operation Indicator
 - Blank: Not equipped with operation indicator
 - N: Equipped with operation indicator
- 7. Certification
 - VD: Certified by UL, CSA, and VDE

$\frac{\text{G3FD}}{1} \xrightarrow{2} \xrightarrow{3} \xrightarrow{4} \xrightarrow{5} \xrightarrow{6} \xrightarrow{7}$

- 1. Basic Model Name
- G3F: Solid State Relay
- 2. Load Power Supply Type D: DC
- D: DC 3. Rated Load Power Supply Voltage
 - X: 50 VDC
 - 1: 100 VDC
- 4. Rated Load Current
 - 02: 2 A
 - 03: 3 A

- 5. Terminal Type
 - S: Plug-in terminals
- 6. Operation Indicator
 - Blank: Not equipped with operation indicator
 - N: Equipped with operation indicator
- 7. Certification
 - VD: Certified by UL, CSA, and VDE



Ordering Information

List of Models

Isolation	Zero cross function	Indicator	Rated output load	Rated input voltage	Model
Photocoupler	Yes Yes		3 A at 100 to 240 VAC (See note 1.)	5 to 24 VDC	G3F-203SN-VD DC5-24
			2 A at 100 to 240 VAC	100/110 VAC	G3F-202SN-VD AC100/110
			(See note 1.)	200/220 VAC	G3F-202SN-VD AC200/220
Phototriac coupler	No		3 A at 100 to 240 VAC	5 VDC	G3F-203SLN-VD DC5
			(See note 1.)	12 VDC	G3F-203SLN-VD DC12
				24 VDC	G3F-203SLN-VD DC24
Photocoupler	_		3 A at 4 to 48 VDC (See note 2.)	5 to 24 VDC	G3FD-X03SN-VD DC5-24
			2 A at 5 to 110 VDC (See note 3.)	100/110 VAC	G3FD-102SN-VD DC5-24
				200/220 VAC	G3FD-102SN-VD AC100/110
				5 to 24 VDC	G3FD-102SN-VD AC200/220
Photocoupler	Yes	No	$(0, \dots, 1, 1)$	4 to 24 VDC	G3F-203S-VD DC4-24
Phototriac coupler	No			5 VDC	G3F-203SL-VD DC5
				12 VDC	G3F-203SL-VD DC12
				24 VDC	G3F-203SL-VD DC24
Photocoupler	-		3 A at 4 to 48 VDC (See note 2.)	4 to 24 VDC	G3FD-X03S-VD DC4-24
			2 A at 5 to 110 VDC (See note 3.)		G3FD-102S-VD DC4-24

Note: 1. Product is labelled "240 VAC".

2. Product is labelled "48 VDC".

3. Product is labelled "110 VDC".

4. When ordering, specify the rated input voltage.

Accessories (Order Separately)

Connection Sockets

Classification	Terminal type	Appearance	Model
Front-mounting	Screw terminals (Terminal cover structure) *		PYFZ-08
	Screw terminals (finger protection structure)		PYFZ-08-E
	Screw terminals (finger protection structure)		PYF08A-N
	Push-In Plus terminal blocks (Socket combination)		PYF-08-PU
Back-mounting	Relays with PCB Terminals		PY08-02

* Terminal cover type is PYCZ-C08. (Order Separately) For details, refer to the Terminal Covers on page 3.

Refer to Common Socket and DIN Track Products for details on Connection Sockets and DIN Track products (sold separately) of your OMRON website. Refer to PYF D-PU/P2RF-D-PU for details on A Push-In Plus Terminal Block Socket of your OMRON website.

G3F/G3FD

Hold-down Clips

	Hold-down Clips		
Classification	Terminal type	Model	Model
For front-mounting	Screw terminals	PYFZ-08	PYC-A1 *
	Screw terminals (finger protection structure)	PYFZ-08-E	
	Screw terminals (finger protection structure)	PYF08A-N	
For back-mounting	Relays with PCB Terminals	PY08-02	PYC-P

* PYC-A1 is provided with two clips.


Terminal Covers

Applicable Socket	Terminal Covers			
Model	Appearance	Model		
PYFZ-08		PYCZ-C08 (2 pcs/set)		

Note: Use these covers in a combination with PYFZ-08.

Dimensions with terminal cover

PYCZ-C08



(Unit: mm)

DIN Track Mounting Parts

Classification/ division	Туре		Appearance	Model
For front-mounting	DIN Tracks	Shallow type, total length: 1 m		PFP-100N
		Shallow type, total length: 0.5 m		PFP-50N
		Deep type, total length: 1 m		PFP-100N2
	End Plate			PFP-M
	Spacer			PFP-S

■Ratings (at an Ambient Temperature of 25°C)

<u>Input</u>

Model	Rated voltage	Operating voltage	Impedance (See note 1.)	Voltage level	
			Input current (See note 2.)	Must operate voltage	Must release voltage
G3F-203SN-VD	5 to 24 VDC	4 to 28 VDC	15 mA max. (See note 2.)	4 VDC max.	1 VDC min.
G3F-202SN-VD	100/110 VAC	75 to 125 VAC	41 kΩ±20%	75 VAC max.	20 VAC min.
	200/220 VAC	150 to 250 VAC	72 kΩ±20%	150 VAC max.	40 VAC min.
G3F-203SLN-VD	5 VDC	4 to 6 VDC	390 Ω±20%	4 VDC max.	1 VDC min.
	12 VDC	9.6 to 14.4 VDC	900 Ω±20%	9.6 VDC max.	
	24 VDC	19.2 to 28.8 VDC	2 kΩ±20%	19.2 VDC max.	
G3FD-X03SN-VD	5 to 24 VDC	4 to 28 VDC	1.5 kΩ ^{+20%} / _{-10%} (See note 1.)	4 VDC max.	
G3FD-102SN-VD	5 to 24 VDC	4 to 28 VDC	1.5 kΩ ^{+20%} / _{-10%} (See note 1.)	4 VDC max.	
	100/110 VAC	75 to 125 VAC	41 kΩ±20%	75 VAC max.	20 VAC min.
	200/220 VAC	150 to 250 VAC	72 kΩ±20%	150 VAC max.	40 VAC min.
G3F-203S-VD	4 to 24 VDC	3 to 28 VDC	15 mA max. (See note 2.)	3 VDC max.	1 VDC min.
G3F-203SL-VD	5 VDC	4 to 6 VDC	390 Ω±20%	4 VDC max.	
	12 VDC	9.6 to 14.4 VDC	900 Ω±20%	9.6 VDC max.	
	24 VDC	19.2 to 28.8 VDC	2 kΩ±20%	19.2 VDC max.	1
G3FD-X03S-VD	4 to 24 VDC	3 to 28 VDC	1.5 kΩ ^{+20%} / _{-10%} (See note 1.)	3 VDC max.	1
G3FD-102S-VD					

Note: 1. The input impedance is given for the maximum operating range. (For example, with the model rated at 5 to 24 VDC, the input impedance is measured at 24 VDC.)

2. Constant-current input circuit.

Output

Model	Rated load	Applicable load				
	voltage	Load voltage range	Load current	Inrush current		
G3F-203SN-VD G3F-203SLN-VD G3F-203S-VD G3F-203SL-VD	100 to 240 VAC	75 to 264 VAC	0.1 to 3 A at 40°C	45 A (60 Hz, 1 cycle)		
G3F-203SN-VD	100 to 240 VAC	75 to 264 VAC	0.1 to 2 A at 40°C	45 A (60 Hz, 1 cycle)		
G3FD-X03SN-VD G3FD-X03S-VD	4 to 48 VDC	3 to 52.8 VDC	0.1 to 3 A at 40°C	18 A (10 ms)		
G3FD-102SN-VD G3FD-102S-VD	5 to 110 VDC	3 to 125 VDC	0.1 to 2 A at 40°C	10 A (10 ms)		


G3F/G3FD


Characteristics

Item	G3F-203SN-VD G3F-202SN-VD G3F-203S-VD	G3F-203SLN-VD G3F-203SL-VD	G3FD-X03SN-VD G3FD-X03S-VD	G3FD-102SN-VD	G3FD-102S-VD
Operate time	1/2 of load power source cycle + 1 ms max. (DC input) 3/2 of load power source cycle + 1 ms max. (AC input)	1 ms max.	0.5 ms max.	0.5 ms max. (DC input) 20 ms max. (AC input)	0.5 ms max.
Release time	1/2 of load power source cycle + 1 ms max. (DC input) 3/2 of load power source cycle + 1 ms max. (AC input)	1/2 of load power source cycle + 1 ms max.	2 ms max.	2.5 ms max. (DC input) 20 ms max. (AC input)	2.5 ms max.
Output ON voltage drop	1.6 V (RMS) max.		1.5 V max.		
Leakage current	5 mA max. (at 100 VAC) 10 mA max. (at 200 VAC)	2.5 mA max. (at 100 VAC) 5 mA max. (at 200 VAC)	5 mA max. (at 50 VDC)	0.1 mA max. (at 100 VDC)	0.1 mA max. (at 100 VDC)
Insulation resistance	100 M Ω min. (at 500 V	VDC)	·		
Dielectric strength	2,000 VAC, 50/60 Hz	for 1 min	1,500 VAC, 50/60 Hz fc	or 1 min	
Vibration resistance	Destruction: 10 to 55	to 10 Hz, 0.75-mm sin	gle amplitude		
Shock resistance	Destruction: 1,000 m/	s ²			
Ambient temperature	Operating: –30°C to 8 Storage: –30°C to 1	0°C (with no icing or o 00°C (with no icing or			
Ambient humidity	Operating: 45% to 85	%			
Certified standards	UL (File No.E64562), CSA (File No.LR35535) VDE (Certificate No.40000159, EN60947-4-3 (G3F-VD) No.40046471, EN62314 (G3FD-VD)				
EMC	Emission: EN55011 Group 1 Class B Immunity: EN61000-6-2				
Weight	Approx. 50 g				
MTTFd (Reference value)	1,000 years min.				

Engineering Data

Load Current vs. Ambient Temperature Characteristics





Ambient temperature (°C)

G3F/G3FD


One Cycle Surge Current: Non-repetitive


Non-repetitive (Keep the inrush current to half the rated value if it occurs repetitively.)

G3F-203SN-VD/203S-VD/202SN-VD/

G3FD-X03SN-VD/X03S-VD

G3FD-102SN-VD/102S-VD







Dimensions

Note: All units are in millimeters unless otherwise indicated.

Relay



Terminal Arrangement/ Internal Connections



- Note: 1. The plus and minus symbols shown in parentheses are for DC loads.
 - 2. With AC input, the input side has no polarity.
 - 3. The load is possible to connect either + side or side.

Accessories (Order Separately)

Connection Socket

Hold-down Clips

Terminal Covers

DIN Track Mounting Parts

Refer to Products Related to Common Sockets and DIN Tracks for precautions on the applicable Sockets of your OMRON website. Refer to PYF-D-PU/P2RF-D-PU for precautions on Push-In Plus Terminal Block Sockets of your OMRON website.

Safety Precautions

Be sure to read 'the Common Precautions' in the website at the following URL: *http://www.ia.omron.com/.*

Refer to Safety Precautions for All Solid State Relays of your OMRON website.

Refer to Products Related to Common Sockets, Terminal Covers and DIN Tracks for precautions on the applicable Sockets of your OMRON website.

Refer to PYF-_-PU/P2RF-_-PU for precautions on Push-In Plus Terminal Block Sockets of your OMRON website.

Precautions for Correct Use

Please observe the following precautions to prevent failure to operate, malfunction, or undesirable effect on product performance.

Connection

The SSR for DC switching use can connect to a load regardless of the polarity of the positive and negative output terminals.

Close Mounting of Multiple Relays

If multiple Relays are mounted side by side, be aware that the outer wall of each SSR works as a heat sink.


The SSR casing serves to dissipate heat. Install the Relays so that they are adequately ventilated. If poor ventilation is unavoidable, reduce the load current by half.

Protective Terminal

When using for AC inductive loads, connect the load terminals of the SSR to an inrush absorber (varistor).

EMC Directive Compliance

 AC-switching models comply with EMC Directives under the following conditions.



- Connect a varistor between the output terminals.
- Connect a film capacitor to the load power supply.
- The input cable must be less than 3 m.
- 2. DC-switching models comply with EMC Directives under the following conditions.

Less than 10 m	ı			
0			Load	٦
Input	G3FD-VD	Output		Ť
0				

• The input cable must be less than 10 m.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

In the interest of product improvement, specifications are subject to change without notice.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company