

cts AMR - datasheet

low payload

Autonomous mobile robot

www.group-cts.de



LD90 RG

Robot-Type	Mobile Robot
mobile Platform	LD90
Payload	up to 50 kg, dependent on used options/customizing
Conveyor type	Frontloader roller
Dimensions L x W/D x H (ca.)	778 x 625 x 1800 mm
Max. overall weight	157 kg
Possible Dimension on transportation goods	Standard: 600 x 400mm / 2x 300 x 400mm With options up to 900 x 600mm
Areas of Application	KLT-Box, Blister, Tray, Carrier transport, e.g. SMT-Reels to the lines, SEMI-goods to Back-End, Finished goods to warehouse
Transfer / handover height	Standard: 800 mm (Customizable)
Height adjustability	Optional (another fixed height)
Lift capability	No
Lifting speed	-
Interface conveyor to vehicle	Digital I/O, Ethernet
HMI	platform onboard HMI (line based)
Wifi	2.4 Ghz/ 5Ghz; 802.11 a/b/g
Battery	24 VDC Life P04, 72 Ah, 2000 recharges
Maximum speed	up to 1,34 m/s
Navigation / orientation	via Lidar
Class	IP20
Environment: Humidity	Moisture 5 to 95%, non-condensing
Environment: Temperature	5-40°C
Max. Traverse	max. 15mm
Max. Angle	up to 1:12 (payload dependent)
Floor conditions	Clean, swept hall and dry floor
Minimum floor flatness	surface-ready and smooth floor according to FEM 9.831 / 9832, maximum +/- 3mm over the entire mounting surface
Environment	not intended for use in hazardous environments (explosive Gas, water, dust, oil mist)
Drive unit	2 wheel driven with 4 helper-caster-wheels
Turnaround radius	0 mm
Occupation sensor detect if unloading place is free	Yes
Full ESD conformity	Optional
Conveyor speed adjustable	Yes
Adjustable side guide rails	Yes
Sensor for load detection	Yes
Optical and acoustical signal unit	Yes
Emergency and acknowledge buttons	Yes
Detection of vertical obstacles above Lidar height	Yes, via side lasers
Opposite station available sensor	Yes
Material moved sensor	Yes

