

# mobERT® C90



\*Darstellung zeigt beispielhafte Produkt-Konfiguration.

Der mobERT®-C90 transportiert Ihre Ladungsträger zuverlässig und kann sie linear aufnehmen und abgeben.

Robuste und bewährte Komponenten unseres Schlüsselpartners OMRON sorgen dafür, dass der mobERT® den rauen Industriealltag leistungsfähig meistert und auch Reinraumfähigkeit besitzt.

Der C90 lässt sich passend zu Ihren Bedürfnissen konfigurieren. Wahlweise mit Förder-, Gurtband oder Hubeinheit sowie Übergabehöhen ab 50cm.

## GESCHWINDIGKEIT\*

1,35 m pro Sekunde

## LADEKAPAZITÄT\*

72 Ah

## MAX. ZULADUNG\*

30 kg

## DIMENSIONEN\*

L 1000 mm, B 740 mm, H 650 mm


## LAUFZEIT\*

bis zu 10 h

## GEWICHT\* (CA.)

122 kg

## KONTAKT



[www.engrotec-solutions.de](http://www.engrotec-solutions.de)

# mobERT® C90



\*Illustration shows exemplary product configuration and special equipment.

The mobERT®-C90 reliably transports your load carriers and can pick them up and deliver them in a linear fashion.

Robust and proven components from our key partner OMRON ensure that the mobERT® masters the rough everyday industrial conditions efficiently and also has clean room capability.

The C90 can be configured to suit your needs.

Optionally with conveyor, belt or lifting unit as well as transfer heights from 50cm.

#### **SPEED\***

1.35 m per Second

#### **CHARGING CAPACITY\***

72 Ah

#### **MAX. PAYLOAD\***

30 kg

#### **DIMENSIONS\***

L 1000 mm, W 740 mm, H 650 mm

#### **RUNNING TIME\***

up to 10 h

#### **WEIGHT\* (CA.)**

122 kg

#### **CONTACT**



[www.engrotec-solutions.de](http://www.engrotec-solutions.de)