

OMRON

Model E3FA-□□□□

PHOTOELECTRIC SENSOR

INSTRUCTION MANUAL

Thank for you selecting OMRON product. This sheet primarily describes precautions required in installing and operating the product.

Before operating the product, read the sheet thoroughly to acquire sufficient knowledge of the product. For your convenience, keep the sheet at your disposal.

TRACEABILITY INFORMATION: Representative in EU: Omron Europe B.V. ... Manufacturer: Omron Corporation, Shiokoji Horikawa, Shimogyo-ku, Kyoto 600-8530 JAPAN

The following notice applies only to products that carry the CE mark: Notice: In a residential environment, this product may cause radio interference, in which case the user may be required to take adequate measures.

1898037-6 H

© OMRON Corporation 2012-2024 All Rights Reserved.

Precautions on safety

Meaning of Signal Words

WARNING Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury or may result in serious injury or death. Additionally there may be significant property damage.

CAUTION Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.

Alert statements in this Manual


WARNING This product is not designed or rated for directly or indirectly ensuring safety of persons. Do not use it for such a purpose.

CAUTION Never use the product with an AC power supply. Do not use the product with voltage in excess of the rated voltage. Do not use the product with incorrect wiring. Otherwise, explosion, fire, malfunction may result.


Rating Performance & Nomenclature

Table with columns for Control output (NPN/PNP), Connection method (Pre-wired cable/M12-connector), Sensing method (Through-beam, Diffuse-reflective, etc.), Sensing distance, and Ambient conditions (Temperature, Humidity, etc.).

Output Circuit diagram




Dimensions




额定性能及命名规则

Table with columns for Control output (NPN/PNP), Connection method (Wiring/M12-connector), Sensing method, Sensing distance, and Ambient conditions.

输出回路



外形尺寸



Precautions for safe use

- 1. Do not use the sensor under the environment with explosive, flammable or corrosive gas.
2. Do not use the sensor under the oil or chemical environment.
3. Do not use the sensor in the water, rain or outdoors.
4. Do not use the sensor in the environment where humidity is high and condensation may occur.
5. Do not use the sensor under the environment under the other conditions in excess of rated.
6. Do not use the sensor in place that is exposed by direct sunlight.
7. Do not use the sensor in place where the sensor may receive direct vibration or shock.
8. Do not use the thinner, alcohol, or other organic solvents.
9. Never disassemble, repair nor tamper with the sensor.
10. Please process it as industrial waste.

Precautions for correct use

- 1. Laying Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in malfunction or damage due to conduit or use shielded cable.
2. Do not pull on the cable with excessive force.
3. If a commercial switching regulator is used, ground the FG (frame ground) terminal.
4. The sensor will be available 100 ms after the power supply is tuned ON. Start to use the sensor 100ms or more after turning ON the power supply.
5. Output pulses may be generated even when the power supply is OFF. Therefore, it is recommended to first turn OFF the power supply for the load or the load line.

Suitability for Use

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS.

OMRON Corporation Industrial Automation Company Tokyo, JAPAN Contact: www.ia.omron.com. Includes regional headquarters information for Europe, USA, Asia, and China.

Oct, 2014

安全上的要点

- 以下项目在安全确保方面非常重要, 请必须遵守。
1. 请勿在具有可燃性、爆炸性或腐蚀性气体的环境下使用。
2. 请勿在油或化学品环境下使用。
3. 请勿在水中、雨中和室外使用。
4. 请勿在湿度高的环境条件下使用, 可能会产生结露。
5. 请勿在其他超过规格值的环境条件下使用。
6. 请勿在日光直射场所使用。
7. 请勿在振动或冲击能直接传达至传感器的场所使用。
8. 请勿使用稀释剂、酒精、或其他有机溶剂。
9. 请勿擅自拆卸、修理、改造本产品。
10. 废弃时, 请作为工业废弃物处理。

使用上的注意

- 1. 电力线、动力线与传感器使用同一配线管或者配线槽时, 会由于感应引起误动作或者产品损坏, 原则上请分开配线或者使用屏蔽线。
2. 对导线部施加的力不得超过额定值。
3. 使用市场上销售的开关整流器时, 请将FG(frame ground)端子接地。
4. 从接通电源到传感器可正常检测的时间是100ms, 所以请在通电100ms后再使用。
5. 由于即使在切断电源时也可能发生输出脉冲, 因此建议先切断负载或负载线的电源。

承诺事项

本公司产品是作为工业通用品而设计制造的。因此, 不适用于以下用途, 当本公司产品被使用于以下用途时, 本公司不做任何保证。

技术咨询 欧姆龙(中国)有限公司 地址: 中国上海市浦东新区银城中路200号 中银大厦2115室 电话: (86) 21-6023-0333 技术咨询热线: 400-820-4535 网址: http://www.fa.omron.com.cn

OMRON

型号

E3FA-□□□□

光电传感器

使用说明书

感谢您选择欧姆龙产品。使用时, 请务必遵守以下内容。
· 由具备一定电气知识的人员使用。
· 使用前, 请仔细阅读本说明书, 充分了解产品。
· 为了您的方便, 请妥善保管好本说明书。

© OMRON Corporation 2012-2024 All Rights Reserved.

安全上的注意

警告表示的意思

警告 如果不正确使用的话, 此危险会导致轻度或者中度的伤害, 也可能导致重伤或者死亡的发生, 并且造成重大的财物损失。

注意 如果不正确使用的话, 此危险会导致轻度或者中度的伤害, 并且造成财物损失。

警告表示

警告 禁止将本品作为直接或间接确保人身安全的用途使用。

注意 请勿将本产品连接AC电源。电源电压必须在额定值内。使用时如不正确接线, 可能会引发爆炸、火灾、机器故障。