

Ref. Shaft diameter [mm]

Capacity [kW]			Frame No. (Foot mounting)		Flange No. (Flange mounting)		Shaft diameter [mm]
2 poles	4 poles	6 poles	IP2X	IP4X	IP2X	IP4X	
0.75	0.75	-	80M		-	FF165	19
1.1	1.1	0.55	90L		-		24
1.5	1.5	0.75			FF165		
2.2	-	-					
-	2.2	1.1	100L		FF215		28
-	-	1.5					
3.7	3.7	2.2	112M				
5.5	5.5	3.7	132S		FF265		38
7.5	-	-					
-	7.5	5.5					
11	-	-	160M		FF300		42
15	-	-					
-	11	7.5					
18.5	-	-	160L				
-	15	11					
22	18.5	-	160L	180M	FF350	FF350	48
-	22	15	-		-		
-	22	15	180M		-	-	
30	-	-		180L	FF350	FF350	55
-	30	18.5					
-	-	22	-	-			
37	-	-	180L	200L	FF400	FF400	
-	-	22		-		-	
-	37	30		200L		-	FF400
-	-	37			-	-	
-	-	37	200M	-	FF500	-	65

※Shaft diameters on the table is guide value referenced from IEC 60072-1.
Please check actual dimensions before monitoring from motor catalog.