

Programmable Controller

CP2E

Micro PLC designed to support data collection and Machine to Machine communication

- Network Model features Ethernet connectivity
 - + 4-axis positioning: CP2E-N type
- Standard Model features axis control: CP2E-S type
- Essential Model features basic control: CP2E-E type




Features


- Two built-in Ethernet ports with Ethernet switching function: Ready for Machine to Machine communication (CP2E-N type)
- Up to three serial ports: Open connectivity to serial devices (CP2E-N type)
- Four-axis positioning function with linear interpolation (CP2E-N type)
- Battery-free operation and backup reduce maintenance
- Function blocks and structured text improve programming efficiency
- Operating temperature range from -20 to 60 °C for reliable use in special applications
- Input/output terminal LED indicators for quick troubleshooting

System Configuration


N□□-type CPU Unit




S□□-type CPU Unit



E□□-type CPU Unit



Model Number Structure



Ordering Information

Applicable standards

Refer to the OMRON website (www.ia.omron.com) or ask your OMRON representative for the most recent applicable standards for each model.

CPU Unit

CP2E-N-type/Network model

				Specific	cations					
Number of points	Power Supply	Inputs	Outputs	Output	Program	Data memory	Current co	nsumption	Model	
	Fower Supply	iliputs	Outputs	type	capacity	capacity	5 VDC	24 VDC		
CPU Units with				Relay			0.15 A	0.05 A	CP2E-N14DR-A	
14 points	100 to 240 VAC			Transistor (sinking)			0.21 A	0.02 A	CP2E-N14DT-A	
· · · · · · · · · · · · · · · · · · ·		8 points	6 points	Relay			0.15 A	0.05 A	CP2E-N14DR-D	
	24 VDC			Transistor (sinking)			0.21 A	0.02 A	CP2E-N14DT-D	
				Transistor (sourcing)			0.22 A	0.02 A	CP2E-N14DT1-D	
CPU Units with				Relay			0.17 A	0.06 A	CP2E-N20DR-A	
20 points	100 to 240 VAC			Transistor (sinking)			0.27 A	0.02 A	CP2E-N20DT-A	
animir"		12 points	8 points	Relay			0.17 A	0.06 A	CP2E-N20DR-D	
	24 VDC		Оронна	Transistor (sinking)			0.27 A	0.02 A	CP2E-N20DT-D	
				Transistor (sourcing)			0.26 A	0.02 A	CP2E-N20DT1-D	
CPU Units with		18 points	s 12 points	Relay	10K steps (FB capacity: 10K steps)	16K words	0.41 A	0.07 A	CP2E-N30DR-A	
30 points	100 to 240 VAC			Transistor (sinking)			0.52 A	0.03 A	CP2E-N30DT-A	
- minima.	24 VDC			Relay			0.37 A	0.07 A	CP2E-N30DR-D	
				Transistor (sinking)			0.51 A	0.03 A	CP2E-N30DT-D	
				Transistor (sourcing)			0.51 A	0.03 A	CP2E-N30DT1-D	
CPU Units with				Relay			0.39 A	0.09 A	CP2E-N40DR-A	
40 points	100 to 240 VAC	40 VAC		Transistor (sinking)			0.59 A	0.03 A	CP2E-N40DT-A	
- minimum.		24 points	16 points	Relay			0.39 A	0.09 A	CP2E-N40DR-D	
	24 VDC			Transistor (sinking)		0.59 A	0.03 A	CP2E-N40DT-D		
				Transistor (sourcing)			0.59 A	0.03 A	CP2E-N40DT1-D	
CPU Units with				Relay			0.44 A	0.13 A	CP2E-N60DR-A	
60 points	100 to 240 VAC			Transistor (sinking)			0.71 A	0.03 A	CP2E-N60DT-A	
- minimum minimum		36 points	24 points	Relay			0.41 A	0.13 A	CP2E-N60DR-D	
- Special Control	24 VDC		, ,	Transistor (sinking)			0.71 A	0.03 A	CP2E-N60DT-D	
				Transistor (sourcing)			0.71 A	0.03 A	CP2E-N60DT1-D	

CP2E-S-type/Standard model

				Specific	cations							
Number of points	Power Supply	Inputs	Outputs	Output	Program	Data memory	Current co	nsumption	Model			
	Power Supply	iliputs	Outputs	type	capacity	capacity	5 VDC	24 VDC				
CPU Units with 30 points	100 to 240 VAC			Relay		8K words	0.12 A	0.07 A	CP2E-S30DR-A			
anning!	24.1/00	18 points	12 points	Transistor (sinking)	1					0.00 4	0.00.4	CP2E-S30DT-D
	24 VDC			Transistor (sourcing)			0.28 A	0.02 A	CP2E-S30DT1-D			
CPU Units with 40 points	100 to 240 VAC			Relay			0.13 A	0.09 A	CP2E-S40DR-A			
Summing!	24 VDC	24 points	16 points	Transistor (sinking)	8K steps (FB capacity:		8K words	0.24 A	0.34 A 0.02 A	CP2E-S40DT-D		
	24 VDC			Transistor (sourcing)	8K steps)			0.34 A		CP2E-S40DT1-D		
CPU Units with 60 points	100 to 240 VAC			Relay				0.16 A	0.13 A	CP2E-S60DR-A		
annimum min	24 VDC	36 points	24 points	Transistor (sinking)			0.49.4	0.48 A 0.02 A	CP2E-S60DT-D			
	24 VDC			Transistor (sourcing)			0.48 A		CP2E-S60DT1-D			

CP2E-E-type/Essential model

				Specifi	cations				
Number of points	Power Supply	Inputs	Outputs	Output Program		Data memory	Current co	nsumption	Model
	Fower Supply	iliputs	Outputs	type	capacity	capacity	5 VDC	24 VDC	
CPU Units with 14 points		8 points	6 points	Relay			0.06 A	0.04 A	CP2E-E14DR-A
CPU Units with 20 points		12 points	8 points	Relay			0.08 A	0.06 A	CP2E-E20DR-A
CPU Units with 30 points	100 to 240 VAC	18 points	12 points	Relay	4K steps (FB capacity: 4K steps)	4K words	0.12 A	0.07 A	CP2E-E30DR-A
CPU Units with 40 points		24 points	16 points	Relay			0.13 A	0.09 A	CP2E-E40DR-A
CPU Units with 60 points		36 points	24 points	Relay			0.16 A	0.13 A	CP2E-E60DR-A

Optional Products

Battery

Product name	Specifications	Model
Battery		
	Mounted in an N/S□□-type CPU Unit. Mount the Battery when using the clock function. A Battery cannot be mounted to an E□□-type CPU Unit.	CP2W-BAT02

Option Board

Product name	Specifications		rent mption	Model	
. roduct name	opositionio	5 VDC	24 VDC		
RS-232C Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as an RS-232C port. Maximum transmission distance: 15 m	0.04 A		CP1W-CIF01	
Non-isolated RS-422A/485 Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as an RS-422A/485 port. Maximum transmission distance: 50 m	0.04 A		CP1W-CIF11	
solated RS-422A/485 Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as an RS-422A/485 port. Maximum transmission distance: 500 m	0.04 A		CP1W-CIF12-V1	
RS-232C&RS-232C Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as two RS-232C ports. Maximum transmission distance: 15 m	0.04 A		CP2W-CIFD1	
RS-232C&RS-485 Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as one RS-232C port and one isolated RS-485 port. Maximum transmission distance: 15 m (RS-232C) 500 m (RS-485)	0.06 A		CP2W-CIFD2	
RS-485&RS-485 Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as two isolated RS-485 ports. Maximum transmission distance: 500 m	0.08 A		CP2W-CIFD3	
Analog Input Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as an analog input module. • 2 analog inputs 0 to 10 V (Resolution: 1/4000) 0 to 20 mA (Resolution: 1/2000)	0.02 A		CP1W-ADB21	
nalog Output Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as an analog output module. • 2 analog outputs 0 to 10 V (Resolution: 1/4000)	0.06 A		CP1W-DAB21V	
Analog Input/Output Option Board	Mounted in the option slot of an N□□-type CPU Unit and can be used as an analog input/output module. • 2 analog inputs 0 to 10 V (Resolution: 1/4000) 0 to 20 mA (Resolution: 1/2000) • 2 analog outputs 0 to 10 V (Resolution: 1/4000)	0.08 A		CP1W-MAB221	

- Note: 1. Maximum one Analog Option Board can be mounted on an N□□-type CPU Unit.

 2. The CP1W-ME05M Memory Cassette, CP1W-DAM01 LCD Option Board, and CP1W-CIF41 Ethernet Option Board cannot be used with the CP2E CPU Unit.
 - **3.** Option Boards cannot be used with the E/S□□-type CPU Unit.

Expansion I/O Units and Expansion Units (for E30/40/60, S30/40/60, or N30/40/60 CPU Units) E14/20 or N14/20 CPU Units do not support Expansion I/O Units and Expansion Units.

Unit type	Product name			Specifications			rent ption (A)	Model
		Inputs	Outputs	Output type		5 V	24 V	
	Input Unit	8		24 VDC Input		0.018		CP1W-8ED
	Output Units		Relay			0.026	0.044	CP1W-8ER
			8	Transistor (sinking)		0.075		CP1W-8ET
			0	Transistor (sourcing)		0.075		CP1W-8ET1
	a			Relay		0.042	0.090	CP1W-16ER
			16	Transistor (sinking)		0.076		CP1W-16ET
P1W Expansion O Units	FIREMEDIA			Transistor (sourcing)		0.076		CP1W-16ET1
· Cilico	Romana o			Relay		0.049	0.131	CP1W-32ER
			32	Transistor (sinking)		0.113		CP1W-32ET
	- A serversories			Transistor (sourcing)		0.113		CP1W-32ET1
	I/O Units			Relay		0.103	0.044	CP1W-20EDR1
	e e e e e e e e e e e e e e e e e e e	12	8	Transistor (sinking)		0.130		CP1W-20EDT
	Turner C	'-		Transistor (sourcing)		0.130		CP1W-20EDT1
	Pantara C			Relay		0.080	0.090	CP1W-40EDR
		24	16	Transistor (sinking)		0.160		CP1W-40EDT
	Famound			Transistor (sourcing)		0.160		CP1W-40EDT1
Ana	Analog Input Unit	4CH		Input range: 0 to 5 V, 1 to 5 V, 0 to 10 V, ±10 V,	Resolution: 1/6000	0.100	0.090	CP1W-AD041
	il — — — — — — — — — — — — — — — — — — —			0 to 20 mA, or 4 to 20 mA.	Resolution: 1/12000	0.100	0.050	CP1W-AD042
	Analog Output Unit		2CH		Resolution: 1/6000	0.040	0.095	CP1W-DA021
			4CH	Output range: 1 to 5 V, 0 to 10 V, ±10 V, 0 to 20 mA, or 4 to 20 mA.	Resolution: 1/6000	0.080	0.124	CP1W-DA041
	(MATRICE)				Resolution: 1/12000	0.070	0.160	CP1W-DA042
	Analog I/O Unit	4CH	4CH	Input range: 0 to 5 V, 1 to 5 V, 0 to 10 V, ±10 V,	Resolution: 1/12000	0.120	0.170	CP1W-MAD44
P1W Expansion		4CH	2CH	0 to 20 mA, or 4 to 20 mA. Output range: 1 to 5 V, 0 to 10 V, ±10 V,	Resolution: 1/12000	0.120	0.120	CP1W-MAD42
nits	Section N	2CH	1CH	0 to 20 mA, or 4 to 20 mA.	Resolution: 1/6000	0.083	0.110	CP1W-MAD11
	Temperature Sensor Unit	2CH		Sensor type: Thermocouple		0.040	0.059	CP1W-TS001
		4CH 2CH		Sensor type: Thermocouple Sensor type: Platinum resista thermometer	ance	0.040	0.059	CP1W-TS101
	Wasters W	4CH		(Pt100 or JPt10 Sensor type: Platinum resista thermometer (Pt100 or JPt10	ance	0.054	0.073	CP1W-TS102
	in the second second	4CH		Sensor type: Thermocouple (J or K) 2channels can be used as analog input. Input range: 1 to 5 V, 0 to 10 V, 4-20 mA	Resolution: 1/12000	0.070	0.030	CP1W-TS003
		12CH		Sensor type: Thermocouple	(Lor K)	0.080	0.050	CP1W-TS004

I/O Connecting Cable

Product name	Specifications	Model
I/O Connecting Cable	80 cm (for CP1W Expansion I/O Units and Expansion Units) Only one I/O Connecting Cable can be used in each PLC.	CP1W-CN811

Recommended Ethernet Communications Cables

For the Ethernet communications cable specifications, refer to page 26.

	Item	Recommended manufacturer	Cable length (m)	Model	
	Cable with Connectors on Both Ends		OMRON	0.3	XS6W-6PUR8SS30CM-YF
	(RJ45/RJ45) Standard RJ45 plug type *1		0.5	XS6W-6PUR8SS50CM-YF	
Wire Gauge and Number of Pairs:	Cable color: Yellow *2		1	XS6W-6PUR8SS100CM-YF	
AWG26, 4-pair Cable Cable Sheath material: PUR			2	XS6W-6PUR8SS200CM-YF	
			3	XS6W-6PUR8SS300CM-YF	
			5	XS6W-6PUR8SS500CM-YF	
	Cable with Connectors on Both Ends	OMRON	0.3	XS5W-T421-AMD-K	
	(RJ45/RJ45) Rugged RJ45 plug type *1		0.5	XS5W-T421-BMD-K	
Wire Gauge and Number of Pairs:	Cable color: Light blue		1	XS5W-T421-CMD-K	
AWG22, 2-pair cable	All I		2	XS5W-T421-DMD-K	
	20		5	XS5W-T421-GMD-K	
			10	XS5W-T421-JMD-K	

^{*1.} Cables with standard RJ45 plugs are available in the following lengths: 0.2 m, 0.3 m, 0.5 m, 1 m, 1.5 m, 2 m, 3 m, 5 m, 7.5 m, 10 m, 15 m, 20 m. Cables with rugged RJ45 plugs are available in the following lengths: 0.3 m, 0.5 m, 1 m, 2 m, 3 m, 5 m, 10 m, 15 m. For details, refer to the *Industrial Ethernet Connectors Catalog* (Cat. No. G019).

RS-232C Connecting Cable

Name	Specifications	Model	
	Connection cable with programmable terminal NB / NS	Length: 2 m	XW2Z-200T
PT-to-PLC	For CP2E-N+CP1W-CIF01	Length: 5 m	XW2Z-500T
Connecting Cable	Connection cable with programmable terminal NB / NS	Length: 2 m	XW2Z-200T-3
	For CP2E-S/E, CP2E-N+CP2W-CIFD1/CIFD2	Length: 5 m	XW2Z-500T-3

DIN Track Accessories

	Name	Specifications	Model
		Length: 0.5 m; Height: 7.3 mm	PFP-50N
DI	N Track	Length: 1 m; Height: 7.3 mm	PFP-100N
		Length: 1 m; Height: 16 mm	PFP-100N2
	End Plate	A stopper to secure the Units on the DIN Track.	PFP-M

Programming Devices

Software

	Specifications			
Product name		Number of licenses	Media	Model
FA Integrated Tool Package CX-One Lite Ver.4.□	CX-One Lite is a subset of the complete CX-One package that provides only the Support Software required for micro PLC applications. CX-One Lite Ver. 4.□ includes Micro PLC Edition CX-Programmer Ver.9.□.	1 license	DVD	CXONE-LT01D-V4
FA Integrated Tool Package CX-One Package Ver. 4.□	CX-One is a comprehensive software package that integrates Support Software for OMRON PLCs and components. CX-One Ver. 4.□ includes CX-Programmer Ver. 9.□.	1 license * 1	DVD	CXONE-AL01D-V4

- Note: 1. For details, refer to the CX-One Catalog (Cat. No. R134), visit your local OMRON website.

 2. CP2E CPU Units are supported by CX-One version 4.51 or higher and CX-Programmer version 9.72 or higher.
 - **3.** The CX-One and CX-One Lite cannot be simultaneously installed on the same computer.

^{*2.} Cable colors are available in yellow, green, and blue.

^{*1.} Multi licenses (3, 10, 30, or 50 licenses) and DVD media without licenses are also available for the CX-One.

CP2E

General Specifications

Item		AC power supply	DC power supply			
Model		CP2E-□□□□□-A	CP2E-□□□D□-D			
Enclosure		Mounted in a panel				
Dimensions (H	× D × W)	CPU Unit with 14 or 20 I/O points (CP2E-□14/20D□-□): 90mm *1 ×80mm *2 × 86mm CPU Unit with 30 I/O points (CP2E-□30D□-□): 90mm *1 × 80mm *2 × 130mm CPU Unit with 40 I/O points (CP2E-□40D□-□): 90mm *1 × 80mm *2 × 150mm CPU Unit with 60 I/O points (CP2E-□60D□-□): 90mm *1 × 80mm *2 × 195mm				
V eight		CPU Unit with 14 I/O points (CP2E14D): 335g m CPU Unit with 20 I/O points (CP2E20D): 340g m CPU Unit with 30 I/O points (CP2E30D): 580g m CPU Unit with 40 I/O points (CP2E40D): 640g m CPU Unit with 60 I/O points (CP2E60D): 780g m	nax. nax. nax.			
	Supply voltage	100 to 240 VAC 50/60 Hz	24 VDC			
	Operating voltage range	85 to 264 VAC	20.4 to 26.4 VDC			
	Power consumption	15 VA/100 VAC max. 25 VA/240 VAC max. (CP2E-□14/20D□-A)	13W max. (CP2E-□14/20D□-D)			
Electrical specifications	Power consumption	50 VA/100 VAC max. 70 VA/240 VAC max. (CP2E-□30/40/60D□-A)	20W max. (CP2E-□30/40/60D□-D) * 4			
	Inrush current	120 VAC, 20 A for 8 ms max. for cold start at room temperature 240 VAC, 40 A for 8 ms max. for cold start at room temperature	24 VDC, 30A for 20 ms max. for cold start at room temperature			
	External power supply *3	Not provided. (CP2E-□14/20D□-A) 24 VDC, 300 mA (CP2E-□30/40/60D□-A)	Not provided.			
	Insulation resistance	$20~\text{M}\Omega$ min. (at 500 VDC) between the external AC terminals and GR terminals	Not csolated between primary and secondary DC power supplies			
	Dielectric strength	2,300 VAC 50/60Hz for 1 min between AC external and GR terminals Leakage current: 5 mA max.	Not csolated between primary and secondary DC power supplies			
	Power interrupt time	10 ms min.	2 ms min.			
	Ambient operating temperature	-20 to 60°C	,			
	Ambient humidity	10% to 90%				
	Atmosphere	No corrosive gas.				
	Ambient storage temperature	-20 to 75°C (excluding battery)				
	Altitude	2,000 m max.				
pplication	Pollution degree	2 or less: Conforms to IEC61010-2-201.				
nvironment	Noise resistance	2 kV on power supply line (Conforms to IEC61000-4-4.)			
	Overvoltage category	Category II: Conforms to IEC61010-2-201.				
	EMC immunity level	Zone B				
	Vibration resistance	Conforms to IEC60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to 150 Hz Acceleration of 9.8 m/s² for 100 min in X, Y, and Z directions (10 sweeps of 10 min each = 100 min total)				
Shock resistance		Conforms to IEC60068-2-27. 147 m/s², 3 times in X, Y, and Z directions				
erminal block		Fixed (not removable)				
erminal screw	size	M3				
pplicable stan	dards	Conforms to EC Directives, KC and UL.				
Frounding meth	nod	Ground to 100Ω or less.				

^{*1.} Total of 110 mm with mounting brackets.

The above calculation results show that a DC power supply with a greater capacity is required.

Note: 1. The Expansion I/O Units and Expansion Units work under the same conditions as the CPU Units unless otherwise specified.

^{*2.} Excluding cables.

^{*3.} Use the external power supply to power input devices. Do not use it to drive output devices.

*4. This is the rated value for the maximum system configuration. Use the following formula to calculate power consumption for CPU Units with

Formula: DC power consumption = (5V current consumption × 5 V/70% (internal power efficiency) + 24V current consumption) × 1.1(current fluctuation factor)

Performance Specifications

Item			CP2E-E□□D□-□	CP2E-S□□D□-□	CP2E-N□□D□-□							
Program capac	ity		4K steps	8K steps	10K steps							
FB capacity			4K steps	8K steps	10K steps							
Control method	d		Stored program method	-1								
I/O control met	hod		Cyclic scan with immediate ref	reshing								
Program langu	age		Ladder diagram	-								
Function block			Maximum number of function by Maximum number of instances		s, structured text (ST)							
Instructions			Approximately 220									
Dunanaina	Overhead proce	essing time	0.1 ms 0.15 ms 0.2 ms									
Processing speed	Instruction exec	cution times	LD 0.23 μs MOV 1.76 μs									
	W-series Expansi		CP2E-\ 14/20D\ -\ : None CP2E-\ 30/40/60D\ -\ : 3 units									
Maximum num	ber of I/O points		CP2E-□40D□-□: 160 (40 built									
Built-in input function	High-speed counters	High-speed counter mode/maximum frequency	Incremental Pulse Inputs 100 kHz: 2 counters 10 kHz: 4 counters Up/Down Inputs 100 kHz: 1 counter 10 kHz: 1 counter Pulse + Direction Inputs 100 kHz: 2 counters Differential Phase Inputs (4x) 50 kHz: 1 counter 5 kHz: 1 counter		N14/20D□-□ Incremental Pulse Inputs 100 kHz: 2 counters 10 kHz: 4 counters Up/Down Inputs 100 kHz: 1 counter 10 kHz: 1 counter Pulse + Direction Inputs 100 kHz: 2 counters Differential Phase Inputs (4x) 50 kHz: 1 counter 5 kHz: 1 counter N30/40/60D□-□ Incremental Pulse Inputs 100 kHz: 3 counters 10 kHz: 3 counters Up/Down Inputs 100 kHz: 2 counters Pulse + Direction Inputs 100 kHz: 2 counters Differential Phase Inputs 00 kHz: 2 counters							
		Counting mode	Linear mode Ring mode									
		Count value	32 bits									
		Counter reset modes	Phase Z and software reset Software reset	(excluding increment pulse input	t)							
		Control method	Target matching Range comparison									
	Input interrupts		6 inputs		8 inputs (6 inputs only for 14 I/O points)							
			Interrupt input pulse width: 50 µs min.									
	Quick-response	inputs	6 inputs 8 inputs (6 inputs only for 14 I/O points									
			Input pulse width: 50 μs min.									
	Normal input	Input constants	Delays can be set in the PLC s Set values: 0, 1, 2, 4, 8, 16, or	setup (0 to 32 ms, default: 8 ms). 32 ms								

CP2E

Item			CP2E-E□□D□-□	CP2E-S□□D□-□	CP2E-N□□D□-□			
		Pulse output		Pulse + Direction Mode				
		Frequency		1 Hz to 100kHz : 2 outputs	N14/20D□-□ 1 Hz to 100kHz: 2 outputs N30/40/60D□-□ 1 Hz to 100kHz: 4 outputs			
		Output mode		Continuous mode (for speed Independent mode (for positi				
	Pulse outputs (Models with transistor	Number of output pulses	Pulse output function not included	Relative coordinates: 0000 0 (0 to 2147483647) Absolute coordinates: 8000 0 (-2147483647 to 2147483647)	0000 to 7FFF FFFF hex			
Built-in output	outputs only)	Acceleration/ deceleration curves		Trapezoidal acceleration and de acceleration and deceleration).	eceleration (Cannot perform S-curve			
function		Changing SVs during instruction execution		Only target position can be cha	nged.			
		Origin searches		Included				
		Linear interpolation		None	N14/20D□-□ 2 axes max. N30/40/60D□-□ 4 axes max.			
	PWM output	Frequency		2.0 to 6,553.5 Hz (in increments 32,000 Hz (in increments of 1 Hz	s of 0.1 Hz) with 1 output or 2 Hz to Hz) with 1 output			
	(transistor outputs models only)	Duty factor	PWM output function not included	0.0% to 100.0% (in increments Accuracy: +1%/-0% at 2 Hz to 10 to 32,000 kHz	of 0.1%) 0,000 Hz and +5%/-0% at 10,000 Hz			
		Output mode		Continuous Mode				
	Peripheral USB	port	Conforming to USB 2.0 B-type	None				
		Transmission distance	5 m max.	140110				
	Built-in RS232C	port	Interface: Conforming to EIA RS	S-232C				
		Transmission distance	15 m max.		_			
		Communications method	Half duplex					
		Synchronization	Start-stop					
		Baud rate	1.2, 2.4, 4.8, 9.6, 19.2, 38.4, 57	.6, or 115.2 kbps	None			
Communicatio		Supported protocol	Host Link 1:N NT Link No-protocol mode Serial PLC Links (master, sla Modbus-RTU Easy Master Modbus-RTU Slave	ve)				
ns	Built-in RS485 p (not isolated)	oort		Interface: Conforming to EIA RS-485				
		Transmission distance		50 m max.				
		Communications method		Half duplex				
		Synchronization		Start-stop				
		Baud rate	None	1.2, 2.4, 4.8, 9.6, 19.2, 38.4, 57.6, or 115.2 kbps	None			
		Supported protocol		Host Link 1:N NT Link No-protocol mode Serial PLC Links (master, slave) Modbus-RTU Easy Master Modbus-RTU Slave				

Item			CP2E-E□□D□-□	CP2E-S□□D□-□	CP2E-N□□D□-□
		Number of Option			N14/20D□-□ 1 Option Board
		Boards			N30/40/60D□-□ 2 Option Boards
			-		N14/20D□-□
		Number of serial communications			2 ports max. N30/40/60D□-□
					3 ports max.
		Communications method			Depends on Option Board
		Synchronization	-		Depends on Option Board
		Baud rate			1.2, 2.4, 4.8, 9.6, 19.2, 38.4, 57.6, or 115.2 kbps
Communications	Serial Option port	Mountable Option Boards	None		Serial Communication Option Board with one port One RS-232C port: CP1W-CIF01 (Half duplex/ Start-stop) One RS-422A/485 port (not isolated): CP1W-CIF11 (Half duplex/ Start-stop) One RS-422A/485 port (isolated): CP1W-CIF12-V1 (Half duplex/ Start-stop) Serial Communication Option Board with two ports *1 Two RS-232C ports: CP2W-CIFD1 (Half duplex/ Start-stop) One RS-232C port and one RS-485 port (isolated): CP2W-CIFD2 (Half duplex/ Start-stop) Two RS-485 ports (isolated): CP2W-CIFD3 (Half duplex/ Start-stop) Two RS-485 ports (isolated): CP2W-CIFD3 (Half duplex/ Start-stop) Analog Option Board *2 CP1W-MAB221/ADB21/DAB21V *1. CP2W-CIFD□ can only be mounted on option slot 1. *2. Maximum one Analog Option Board can be mounted on an N□□-type CPU Unit.
		Compatible protocols			Host Link* 1:N NT Link* No-protocol mode Serial PLC Links (master, slave) Modbus-RTU Easy Master Modbus-RTU Slave PORT1 (EX) is not supported.
		Physical layer			100/10BASE-TX (Auto-MDIX)
		Media access methiod			CSMA/CD
		Modulation			Baseband
		Baud rate			100BASE-TX: 100Mbit/s 10BASE-T: 10Mbit/s • Half/full auto-negotiation for each port • Link speed auto-sensing for each port
	Ethernet	Transmission media	None		100BASE-TX Unshielded twisted-pair (UDP) cable Categories: 5, 5e Shielded twisted-pair (STP) cable Categories: 100Ω at 5, 5e Unshielded twisted-pair (UDP) cable Categories: 3, 4, 5, 5e Shielded twisted-pair (STP) cable Categories: 100Ω at 3, 4, 5, 5e
		Transmission distance			100 m (distance between switch and node)
		Protocol			TCP, UDP, APR, ICMP (ping
		Applications	-		only), SNTP, DNS FINS, Socket, SNTP, DNS (Client)
		Number of Ethernet ports			N14/20: 1 port N30/40/60: 2 ports
		Ethernet switch			Layer 2 switch


CP2E

Item		CP2E-E□□D□-□	CP2E-S□□D□-□	CP2E-N□□D□-□							
Number of task	ks	Built-in input interrupt task: I CPU Units)	1 cyclic task 16 interrupt tasks Scheduled interrupt task: Interrupt task 1 (fixed) Built-in input interrupt task: Interrupt task 2 to 9 (IN8 and IN9 can only be used in N20/30/40/60 CPU Units) High-speed counter interrupt task: Interrupt task 1 to 16								
Maximum subi	outine number	128									
Maximum jum	number	128									
Scheduled inte	errupt tasks	1 interrupt task									
Battery service *With CP2W-B	e life AT02 Battery (optional)	Battery cannot be mounted.	CP2W-BAT02 can be mounted. Maximum battery service life: 5 years Guaranteed Lifetime Ambient temperature is 60°C: 13,000 hours (approx. 1. Ambient temperature is 25°C: 43,000 hours (approx. 5)								
Clock		None	Supported. Accuracy (monthly deviation): -4.5 min to -0.5 min (ambient te -2.0 min to +2.0 min (ambient te -2.5 min to +1.5 min (ambient te	emperature: 25°C),							
Memory	Built-in Flash Memory	Ladder programs and parameters are automatically saved to built-in Flash Memory. A section of the Data Memory Area can be saved to the built-in Flash Memory.									
backup	Built-in non-volatile memory			Auxiliary Area (A) are automatically							
	Input Bits	1,600 bits (100 words): CIO 0.0	00 to CIO 99.15 (CIO 00 to CIO 9	9)							
CIO Area	Output Bits	A section of the Data Memory Area can be saved to the built-in Flash Memory. Data Memory Area (D) Holding Area (H) Counter Area (C) and Auviliany Area (A) are automatical									
	Serial PLC Link Words	1,440 bits (90 words): CIO 200	.00 to CIO 289.15 (CIO 200 to CI	O 289)							
Work Area (W)		2,048 bits (128 words): W0.00	to W127.15 (W0 to W127)								
Holding Area (Н)	2,048 bits (128 words): H0.00 t Words H512 to H1535: These	o H127.15 (H0 to 127) words can be used only for function	on blocks.							
Auxiliary Area	(A)		ds): A0.00 to A447.15 (A0 to A44 rds): A448.00 to A959.15 (A448 to								
Temporary Are	ea (TR)	16 bits: TR0 to TR15									
Timer Area (T)		256 timer numbers (T0 to T255 Words T256 to T511: These wo	(separate from counters)) ords can be used only for function	blocks.							
Counter Area (C)	256 counter numbers (C0 to C2 Words C256 to C511: These w	255 (separate from timers)) ords can be used only for function	n blocks.							
Data Memory A	Area (D)	4 K words: D0 to D4095 DM backup: 1,500 words (D0 to D1499)	8 K words: D0 to D8191 DM backup: 7,000 words (D0 to D6999)	16 K words: D0 to D16383 DM backup: 15,000 words (D0 to D14999)							
Index Register	s (IR)	16 registers: IR0 to IR15									
Data Registers	(DR)	16 registers: DR0 to DR15									
Operating mod	les	PROGRAM Mode: Program execution is stopped. Preparations can be executed prior to program execution in this mode. MONITOR Mode: Programs are executed. Some operations, such as online editing, and changes to present values in I/O memory, are enabled in this mode. RUN Mode: Programs are executed. This is the normal operating mode.									

Internal Memory in the CPU Units


CPU Unit Memory Backup Structure

The internal memory in the CPU Unit consists of built-in RAM and built-in Flash Memory. The built-in RAM is used as execution memory and the built-in Flash Memory is used as backup memory.




Part Names and Functions

E-type CPU Unit CP2E-E14/20DR-A



N-type CPU Unit CP2E-N14/20D□-□



Number	Name	Function
(1)	Input terminal block (not removable)	This is the terminal block for inputs such as the power supply input and 24 VDC inputs.
(2)	Input indicators (yellow)	Input status is displayed. An indicator will be ON when the input is ON.
(3)	Peripheral USB port for E□□-type CPU Units	Used to connect to a personal computer for programming and monitoring by the CX-Programmer for CP2E.
(4)	Option Board slot for N□□-type CPU Units	An Option Board can be connected to the slot. • CP1W-CIF01 RS-232C Option Board • CP1W-CIF11 RS-422A/485 Option Board (Maximum transmission distance: 50 m) • CP1W-CIF12-V1 RS-422A/485 Option Board (Maximum transmission distance: 500 m) • CP1W-MAB221/ADB21/DAB21V Analog Option Board • CP2W-CIFD1 Option Board with two RS-232C ports • CP2W-CIFD2 Option Board with one RS-232C port and one RS-485 port (isolated) • CP2W-CIFD3 Option Board with two RS-485 ports (isolated)
(5)	Operation indicators	The CPU Unit's operating status can be confirmed with this indicator.
(6)	Power supply input terminals	Power of 100 to 240 VAC or 24 VDC can be supplied.
(7)	Ground terminal	Protective ground ($\mbox{$\stackrel{\triangle}{\oplus}$}$): To prevent electric shock, ground to 100 Ω or less.
(8)	Input terminals	Input devices such as switches and sensors can be connected.
(9)	Output indicators (yellow)	Output status is displayed. An indicator will be ON when the output is ON.
(10)	Output terminal block (not removable)	This is the terminal block for outputs such as relay outputs and transistor outputs.
(11)	Output terminals	Loads such as lamps, contactors, and solenoid valves can be connected.
(12)	Battery holder for N□□-type CPU Units	A Battery can be installed by opening the cover. (The Battery is optional.)
(13)	Built-in RS-232C port for E□□-type CPU Units	By connecting a PT, the controlled system can be monitored and data can be collected.
(14)	Built-in Ethernet port for N□□-type CPU Units	Used to connect to a personal computer for programming and monitoring by the CX-Programmer for CP2E, or connect to other OMRON PLCs for data exchange.

E/S-type CPU Unit CP2E-E30/40/60DR-A CP2E-S30/40/60D□-□ N-type CPU Unit CP2E-N30/40/60D□-□ (14) Battery (6) Power supply input terminals holder (7) Input terminals (1) Input terminal block (8) Ground (2) Input (4) Option terminal indicators Board slots (9) Expansion I/O Unit connector (3) Peripheral (15) Built-in USB port Ethernet port (5) Operation (10) Output indicators indicators 1) Output (16) Built-in -(18) External supply terminals terminal block RS-232C port (12) Output PORT1A PORT1B (17) Built-in -(13) External power supply RS-485 port input terminals

Number	Name	Function
(1)	Input terminal block (not removable)	This is the terminal block for inputs such as the power supply input and 24 VDC inputs.
(2)	Input indicators (yellow)	Input status is displayed. An indicator will be ON when the input is ON.
(3)	Peripheral USB port for E/S□□-type CPU Units	Used to connect to a personal computer for programming and monitoring by the CX-Programmer for CP2E.
(4)	Option Board slots for N□□-type CPU Units	Option Boards can be connected to the slots. • CP1W-CIF01 RS-232C Option Board • CP1W-CIF11 RS-422A/485 Option Board (Maximum transmission distance: 50 m) • CP1W-CIF12-V1 RS-422A/485 Option Board (Maximum transmission distance: 500 m) • CP1W-MAB221/ADB21V Analog Option Board • CP2W-CIFD1 Option Board with two RS-232C ports • CP2W-CIFD2 Option Board with one RS-232C port and one RS-485 port (isolated) • CP2W-CIFD3 Option Board with two RS-485 ports (isolated)
(5)	Operation indicators	The CPU Unit's operating status can be confirmed with this indicator.
(6)	Power supply input terminals	Power of 100 to 240 VAC or 24 VDC can be supplied.
(7)	Input terminals	Input devices such as switches and sensors can be connected.
(8)	Ground terminal	Protective ground (\oplus): To prevent electric shock, ground to 100 Ω or less. Functional ground (\oplus): If noise is a significant source of errors or if electrical shock is a problem, connect to the protective ground terminal and ground both with a ground of 100 Ω or less (AC power supply only).
(9)	Expansion I/O Unit connector	CP-series Expansion I/O Units or Expansion Units such as Analog I/O Units, and Temperature Sensor Units can be connected.
(10)	Output indicators (yellow)	Output status is displayed. An indicator will be ON when the output is ON.
(11)	Output terminal block (not removable)	This is the terminal block for outputs such as relay outputs, transistor outputs, and the external power supply output.
(12)	Output terminals	Loads such as lamps, contactors, and solenoid valves can be connected.
(13)	External power supply input terminals for S□□-type CPU Units	Power of 20.4V to 26.4 VDC can be supplied to CIO 100.00 and CIO 100.01.
(14)	Battery holder for N/S□□-type CPU Units	A Battery can be installed by opening the cover. (Battery is optional.)
(15)	Built-in Ethernet port for N□□-type CPU Units	Used to connect to a personal computer for programming and monitoring by the CX-Programmer for CP2E, or connect to other OMRON PLCs for data exchange.
(16)	Built-in RS-232C port for E/S□□-type CPU Units	By connecting a PT, the controlled system can be monitored and data can be collected.
(17)	Built-in RS-485 port for S□□-type CPU Units	Communications are possible between an inverter and a PLC by using Modbus-RTU and Serial PLC Links.
(18)	External supply terminals	The external supply terminals output up to 300 mA max at 24 VDC. They can be used as a service power supply for input devices (AC power supply only).

(Bottom View)

Built-in Inputs

Terminal Arrangements

●14 points

AC power supply

CP2E-□14D□-A

	CIO 0																
L	1	L2/N COM		MC	0	1	03		05		07		NC		NC		
	N	С	(a)		0	0	0	2	0	4	0	6	N	С	Ν	С	

L1,L2/N: Power supply terminal

: Protective ground terminal
COM: Common terminal
00 to 07: Input terminal
NC: No connection

DC power supply


CP2E-N14D□-D

	CIO 0																
-	+		- cc		OM 01		1	03		05		07		NC		NC	
	N	С	Ġ	•	0	0	0	2	0	4	0	6	N	С	N	С	

●20 points

AC power supply

CP2E-□20D□-A



L1,L2/N: Power supply terminal

Protective ground terminal
COM: Common terminal
Ot to 11: Input terminal
NC: No connection

DC power supply

CP2E-N20D□-D

+ - COM 01 03 05 07 09	11
NC (=) 00 02 04 06 08	10

+,- : Power supply terminal
: Protective ground terminal
COM : Common terminal
00 to 11 : Input terminal
NC : No connection

●30 points

AC power supply

CI	P2	E-		30	D	□-	A															
			C	OIS	0											CIO	1					
	L1 L2/N COM 01					1	03	3 (15	0	7	0	9	11	0	1	0	3	0	5		
_			00	0 02		2	04		6	08		10	Г	00		02		4	NC	;		

L1, L2/N	: Power supply terminal
COM	: Common terminal
00 to 11	: Input terminal
\$: Functional ground terminal
(-)	: Protective ground terminal
NC	: No connection

DC power supply


CP2E-□30D□-D

		CIO	0											С	Ю	1					
+	-	CC	ОМ	01	0	3	0	5	0	7	0	9	1	1	0	1	0	3	0	5	
NC	;	(1)	00	0	2	0	4	0	6	0	8	1	0	0	0	0	2	0	4	N	С

●40 points

AC power supply

CP2E-□40D□-A



DC power supply

CP2E-□40D□-D

		С	Ю	0												С	Ю	1										
+	-	-	CC	ОМ	0	1	0	3	0	5	0	7	0	9	1	1	0	1	03	3	0	5	0	7	0	9	11	П
N	С	G	b	0	0	0	2	0	4	06	ŝ	0	8	1	0	0	0	02	2	04	1	06	3	0	8	10	5	_

●60 points

AC power supply

CP2E-□60D□-A

		С	10 0								CIO	O 1							С	10 2							
L	.1 L	.2/N	СОМ	0)1 (03	05	07	09	9 1	1	01	03	C)5	07	0	9 1	11	01	0	3 0)5	07	С	9 -	11
	4	(=	5 0	00	02	04	06	3 (08	10	00	0:	2	04	06	3 (08	10	0	0	02	04	06	Τ	08	10	Т

DC power supply

CP2E-□60D□-D

	((CIO ·	1							С	10 2	2						
+	-	COI	И	01	03	0	5 (07	09	11	0	1	03	0	5	07	09	9	11	0	1 0	3 ()5	07	7 0	9 1	11
NC	: (Ð	00	02	,	04	06	0	8 -	10	00	02	2 ()4	06	- 0	18	10	0	0	02	04	O.	6	08	10	Т

Allocating Built-in Input Terminals to Functions

Input terminals are allocated functions by setting parameters in the PLC Setup. Set the PLC Setup so that each terminal is used for only one function.

E20/30/40/60, S30/40/60 or N20/30/40/60 CPU Units

					PLC	Setup		
Terminal	Terminal		rrupt input s iilt-in Input T			ed counter 0 to 5 s uilt-in Input Tab Pa		Origin search settings on Pulse Output 0 to 3 Tab Page
block	number	Normal	Interrupt	Quick		Use		Use
label		Normal input	Interrupt inputs	Quick-response inputs	Increment pulse input	Differential phase ×4 or up/down	Pulse/ direction	Origin search
	00	Normal input 0			Counter 0, increment input	Counter 0, phase A or up input	Counter 0, pulse input	
	01	Normal input 1			Counter 1, increment input	Counter 0, phase B or down input	Counter 1, pulse input	
	02	Normal input 2	Interrupt input 2	Quick-response input 2	Counter 2, increment input	Counter 1, phase A or up input	Counter 0, direction	
	03	Normal input 3	Interrupt input 3	Quick-response input 3		Counter 1, phase B or down input	Counter 1, direction	
	04	Normal input 4	Interrupt input 4	Quick-response input 4	Counter 3, increment input	Counter 0, phase Z or reset input	Counter 0, reset input	
CIO 0	05	Normal input 5	Interrupt input 5	Quick-response input 5	Counter 4, increment input	Counter 1, phase Z or reset input	Counter 1, reset input	
CIO U	06	Normal input 6	Interrupt input 6	Quick-response input 6	Counter 5, increment input			Pulse 0, Origin input signal
	07	Normal input 7	Interrupt input 7	Quick-response input 7				Pulse 1, Origin input signal
	08	Normal input 8	Interrupt input 8 *1	Quick-response input 8 *1				Pulse 2, Origin input signal *2
	09	Normal input 9	Interrupt input 9 *1	Quick-response input 9 *1				Pulse 3, Origin input signal *2
	10	Normal input 10						Pulse 0, Origin proximity input signal
	11	Normal input 11						Pulse 1, Origin proximity input signal
	00	Normal input 12						Pulse 2, Origin proximity input signal *2
CIO 1	01	Normal input 13						Pulse 3, Origin proximity input signal *2
	02 to 11	Normal input 14 to 23						
CIO 2	00 to 11	Normal input 24 to 35						

Note: 1. The same pulse inputs must be used for high-speed counter 0 and high-speed counter 1.

E14 or N14 CPU Units

					PLC Set	up		
Terminal block	Terminal		terrupt input sett Built-in Input Tab			eed counter 0 to 5 se Built-in Input Tab Pag		Origin search settings on Pulse Output 0/1 Tab Page
label	number	Normal	Interrupt	Quick		Use		Use
		Normal input	Interrupt inputs	Quick-response inputs	Increment pulse input	Differential phase ×4 or up/down	Pulse/ direction	Origin search
	00	Normal input 0			Counter 0, increment input	Counter 0, phase A or up input	Counter 0, pulse input	
	01	Normal input 1			Counter 1, increment input	Counter 0, phase B or down input	Counter 1, pulse input	
	02	Normal input 2	Interrupt input 2	Quick-response input 2	Counter 2, increment input	Counter 1, phase A or up input	Counter 0, direction	
CIO 0	03	Normal input 3	Interrupt input 3	Quick-response input 3		Counter 1, phase B or down input	Counter 1, direction	Pulse 0, Origin proximity input signal
CIO U	04	Normal input 4	Interrupt input 4	Quick-response input 4	Counter 3, increment input	Counter 0, Phase Z or reset input	Counter 0, reset input	
	05	Normal input 5	Interrupt input 5	Quick-response input 5	Counter 4, increment input	Counter 1, Phase Z or reset input	Counter 1, reset input	Pulse 1, Origin proximity input signal
	06	Normal input 6	Interrupt input 6	Quick-response input 6	Counter 5, increment input			Pulse 0, Origin input signal
	07	Normal input 7	Interrupt input 7	Quick-response input 7				Pulse 1, Origin input signal

Note: 1. The same pulse inputs must be used for high-speed counter 0 and high-speed counter 1.

^{*1.} Only supported by N□□-type CPU Units. ***2.** Only supported by N30/40/60 CPU Units.

^{2.} High-speed counter 2 cannot be used if the input setting of high-speed counter 0 or high-speed counter 1 is set for differential phase inputs (4×), pulse + direction inputs, or up/down pulse inputs.

^{2.} High-speed counter 2 cannot be used if the input setting of high-speed counter 0 or high-speed counter 1 is set for differential phase inputs (4×), pulse + direction inputs, or up/down pulse inputs.

Built-in Outputs

Terminal Arrangements

●14 points

AC/DC power supply

CP2E-□14D□-□



COM: Common terminal
00 to 05: Output terminal
NC: No connection

●20 points

AC/DC power supply

CP2E-□20D□-□



COM: Common terminal
00 to 07: Output terminal
NC: No connection

COM

●30 points

AC power supply

CP2E-□30D□-A



+,- : External supply terminal
COM : Common terminal
00 to 07 : Output terminal

DC power supply

CP2E-N30D□-D



NC : No connection
COM : Common terminal
00 to 07 : Output terminal

: Common terminal


CP2E-S30DT-D



00-07 : Output terminal
V+ : External power supply input terminal for CIO 100.00/01 (DC24V)
V- : External power supply input terminal for CIO 100.00/01 (0V)

Note: COM(V-) has been connected with V- in an inner circuit.

CP2E-S30DT1-D



Note: COM(V+) has been connected with V+ in an inner circuit.

●40 points

AC power supply

CP2E-□40D□-A



DC power supply

CP2E-N40D□-D



CP2E-S40DT-D



Note: COM(V-) has been connected with V- in an inner circuit.

CP2E-S40DT1-D



Note: COM(V+) has been connected with V+ in an inner circuit.

●60 points AC power supply CP2E-□60D□-A + 00 01 02 04 05 07 00 02 04 05 07 00 02 04 COM COM COM 03 COM 06 COM 01 03 COM 06 COM 01 03 COM 06 CIO 102 CIO 100 CIO 101 DC power supply CP2E-N60D□-D NC 00 01 02 04 05 07 00 02 04 05 07 00 02 04 05 07 NC COM COM COM 03 COM 06 COM 01 03 COM 06 COM 01 03 COM 06 CIO 100 CIO 101 CP2E-S60DT-D V+ 00 01 02 04 05 07 00 02 04 05 07 00 02 04 05 07 00 02 04 05 07 V- COM(V-) COM 03 COM 06 COM 01 03 COM 06 COM 01 03 COM 06 CIO 100 CIO 101 Note: COM(V-) has been connected with V- in an inner circuit. CP2E-S60DT1-D V+ 00 01 02 04 05 07 00 02 04 05 07 00 02 04 05 07 V- COM(V+) COM 03 COM 06 COM 01 03 COM 06 COM 01 03 COM 06 CIO 101 Note: COM(V+) has been connected with V+ in an inner circuit.

Allocating Built-in Output Terminals to Functions

Output terminals are allocated functions by setting parameters in the PLC Setup. Set the PLC Setup so that each terminal is used for only one function.

		Other than those	When a pulse output instruction	PLC Setup	When the PWM instruction is
Output terr	ninal block	shown at the right	(ITPL, SPED, ACC, PLS2, or ORG) is executed	Origin search settings on Pulse Output 0 to 3 Tab Page	executed
Terminal	Terminal	Normal autouta	Fixed duty rati	io pulse output	Variable-duty-factor output
block label	number	Normal outputs	Pulse + Direction Mode	Use	PWM output
	00	Normal output 0	Pulse output 0, pulse		
	01	Normal output 1	Pulse output 1, pulse		PWM output 0
	02	Normal output 2	Pulse output 0, direction		
	03	Normal output 3	Pulse output 1, direction		
CIO 100	04	Normal output 4		Pulse 0, Error counter reset output	
	05	Normal output 5		Pulse 1, Error counter reset output	
	06	Normal output 6		Pulse 2, Error counter reset output *1	
	07	Normal output 7		Pulse 3, Error counter reset output *1	
	00	Normal output 0	Pulse output 2, pulse *1		
	01	Normal output 1	Pulse output 3, pulse *1		
CIO 101	02	Normal output 2	Pulse output 2, direction *1		
	03	Normal output 3	Pulse output 3, direction *1		
	04 to 07	Normal output 12 to 15			
CIO 102	00 to 07	Normal output 16 to 23			

^{*1.} Only supported by N30/40/60 CPU Units.


CP2E


I/O Specifications


Specifications

Item			Specification					
Input type		High-speed counter inputs or normal inputs	High-speed counter inputs, interrupt inputs, quick-response inputs or normal inputs	Normal inputs				
	E/S□□-type and N14 CPU Units	CIO 0.00 and CIO 0.01	CIO 0.02 to CIO 0.07	CIO 0.08 to CIO 0.11, CIO 1.00 to CIO 1.11 and CIO 2.00 to CIO 2.11 *1				
Input bits	N20 CPU Units	CIO 0.00 and CIO 0.01	CIO 0.02 to CIO 0.09	CIO 0.10 to CIO 0.11				
	N30/40/60 CPU Units	CIO 0.00 to CIO 0.03	CIO 0.04 to CIO 0.09	CIO 0.10, CIO 0.11, CIO 1.00 to CIO 1.11 and CIO 2.00 to CIO 2.11 *1				
Applicable	inputs	2-wire and 3-wire sensors						
Input voltag	je	24 VDC, +10% / -15%						
Input imped	lance	3.3 kΩ	3.3 kΩ	4.8 kΩ				
Input curre	nt	7.5 mA (typical)	7.5 mA (typical)	5 mA (typical)				
ON voltage	current/	17.0 VDC min. / 3 mA min.	17.0 VDC min. / 3 mA min.	14.4 VDC min. / 3 mA min.				
OFF voltage	e/current	5.0 VDC max. / 1 mA max.	5.0 VDC max. / 1 mA max.	5.0 VDC max. / 1 mA max.				
ON respons	se time * 2	2.5 μs min.	50 μs max.	1 ms max.				
OFF respon	rse time * 2	2.5 μs min.	50 μs max.	1 ms max.				
Circuit conf	figuration	,	Input indicator Input indicator Incircuits COMI					


- *1. The bits that can be used depend on the model of CPU Unit.
- *2. The response time is the delay caused by hardware. The delay set in the PLC Setup (0 to 32 ms, default: 8 ms) for a normal input must be added to this value.








Differential phase mode



E/S - type: 0.02/0.03 N14/20: 0.02/0.03




Output Specifications for Relay Outputs

CP2E-□□□DR-□

Item			Specification
Maximum sw	itching capa	city	2 A 250 VAC (cosφ= 1) 2 A 24 VDC (4 A/common)
Minimum swi	itching capa	city	10 mA 5 VDC
	Electrical	Resistive load	200,000 operations (24 VDC)
Service life of relay	Electrical	Inductive load	70,000 operations (250 VAC, cosφ = 0.4)
or relay	Mechanica	l	20,000,000 operations
ON response	time		15 ms max.
OFF respons	e time		15 ms max.
Circuit config	guration		Output indicator Output indic

Estimating the Service Life of Relays

Under normal conditions, the service life of output contacts is as shown above. The service life of relays is as shown in the following diagram as a guideline.



Output Specifications for Transistor Outputs (Sinking or Sourcing)

CP2E-N14/20/30/40/60DT(1)-□, CP2E-S30/40/60DT(1)-□

Normal Outputs

	Speci	ification
Item	S□□-type: CIO 100.00 and CIO 100.01 N□□-type: CIO 100.00, CIO 100.01, CIO 101.00 and CIO 101.01	S□□-type: CIO 100.02 to CIO 102.07 *2 N□□-type: CIO 100.02 to CIO 100.07, CIO 101.02 to CIO 102.07 *2
Maximum switching capacity	0.3 A/output, 0.9 A/common *1 4.5 to 30 VDC CP2E-N14D: 1.5 A/Unit CP2E-N20D: 1.8 A/Unit CP2E-S/N30D: 2.7 A/Unit	
Minimum switching capacity	1 mA 4.5 to 30 VDC	
Leakage current	0.1mA max.	_
Residual voltage	0.6 V max.	1.5V max.
ON response time	0.1 ms max.	0.1 ms max.
OFF response time	0.1 ms max.	1 ms max.
Fuse	Not provided.	
External power supply	20.4 to 26.4VDC 30mA max. (N□□-type is not needed)	Not needed
Circuit configuration	Sourcing output model Internal circuits Nout Out Out Out Out Out Out Out	Sinking output model Internal circuits Sourcing output model COM(+) Linternal circuits COM(+) 24 VDC, 4.5 to 30 VDC COM(+) 24 VDC, 4.5 to 30 VDC OUT OUT OUT OUT OUT OUT OUT OU

*1. Also do not exceed 0.9 A for the total of CIO 100.00 to CIO 100.03, which are different common.

***2.** The bits that can be used depend on the model of CPU Unit.

Note: 1. Do not connect a load to an output terminal or apply a voltage in excess of the maximum switching capacity.

Pulse Outputs

	Specification
Item	S□□-type: CIO 100.00 and CIO 100.01 N□□-type: CIO 100.00, CIO 100.01, CIO 101.00 and CIO 101.01
Maximum switching capacity	100 mA 4.5 to 26.4 VDC
Minimum switching capacity	7 mA 4.5 to 26.4 VDC
Maximum output frequency	100 kHz
Output waveform	OFF 90% ON 10% 4μs min. 2μs min. The OFF and ON refer to the output transistor. The output transistor is ON at level "L".

- Note: 1. The load for the above values is assumed to be the resistive load, and does not take into account the impedance for the connecting cable to the load.
 - 2. Due to distortions in pulse waveforms resulting from connecting cable impedance, the pulse widths in actual operation may be smaller than the values shown above.

PWM Output (CIO 100.01)

Item	Specification
Maximum switching capacity	30 mA 4.5 to 26.4 VDC
Maximum output frequency	32 kHz
PWM output accuracy	For ON duty +1%, -0%:10 kHz output For ON duty +5%, -0%: 0 to 32 kHz output
Output waveform	OFF ON $\frac{toN}{T} \times 100\%$ The OFF and ON refer to the output transistor. The output transistor is ON at level "L".

CP2E

Built-in Ethernet

General Specifications (Ethernet)

	Item	Specif	ications
	Туре	100BASE-TX (Auto-MDIX)	10BASE-T (Auto-MDIX)
Number of	Ethernet ports	N14/20 CPU Units: 1 port N30/40/60 CPU Units: 2 ports (Switching Hub ful	nction is built in.)
	Media access method	CSMA/CD	
	Modulation method	Baseband	
	Transmission paths	Star form	
	Bourd mate	100 Mbit/s (100Base-TX) Auto-Negotiation	10 Mbit/s (10Base-T) Auto-Negotiation
Transfer	Baud rate	Half/full auto-negotiation for each port Link speed auto-sensing for each port	•
	Transmission media	 Unshielded twisted-pair (UDP) cable Categories: 5, 5e Shielded twisted-pair (STP) cable Categories: 100Ω at 5, 5e 	 Unshielded twisted-pair (UDP) cable Categories: 3, 4, 5, 5e Shielded twisted-pair (STP) cable Categories: 100Ω at 3, 4, 5, 5e
	Transmission distance	100 m (distance between hub and node)	
Protocols		TCP, UDP, ARP, ICMP (ping only), SNTP, DNS	


FINS Communications Service Specifications

Item		Specification				
Protocol name	FINS/UDP	FINS/TCP				
Number of nodes	254					
Message Length	1016 bytes max.					
Date Length	1004 bytes max.					
Number of buffer	16	16				
	UDP/IP	TCP/IP				
Protocol used		The selection of UDP/IP or TCP/IP is made by means of the FINS/UDP or FINS/TCP button in Built-in Ethernet Tab in the CX-Programmer's PLC Setup.				
Number of connections		3 for user, 1 for CX-Programmer auto connection				
Port number	9600 (default) Can be changed.	9600 (default) Can be changed.				
Protection	No	No Yes (Specification of client IP addresses when unit is used as a server)				
Local IP address	192.168.250.FINS node address					

Switching Hub for CP2E N□□-type CPU Units

Ethernet	100Base-TX, 10Base-T
Auto MID/MID-X	Yes
Auto negotiation	Yes
Store-and-forward system	Yes
Buffer	32K bytes
MAC address	1000
Broadcast storm detection	Yes
QoS	No
SNMP	No
VLAN	No
IGMP snooping	No
STP (Spanning Tree Protocol)	No
Port mirroring	No

Serial Communication



Note: 1. CP2W-CIFD□ can only be mounted on option slot 1.

Serial Communication Option Board

Model numbers	Port	Maximum transmission distance	Connection method
CP1W-CIF01	One RS-232C port	15m	Connector (D-sub, 9 pin female)
CP1W-CIF11	One RS-422A/485 port (not isolated)	50m	Terminal block (using ferrules)
CP1W-CIF12-V1	One RS-422A/485 port (isolated)	500m	Terminal block (using ferrules)
CP2W-CIFD1	Two RS-232C Ports	15m	Terminal block (using ferrules)
CP2W-CIFD2	One RS-232C port and one RS-485 port (isolated)	15m (RS-232C) 500m (RS-485)	Terminal block (using ferrules)
CP2W-CIFD3	Two RS-485 ports (isolated)	500m	Terminal block (using ferrules)

Built-in RS-232C Port for E/S□□-type CPU Units



Pin	Abbr.	Signal Name	Signal direction
1	SD(TXD)	Send data	Output
2	RD(RXD)	Receive data	Input
3	RS(RTS)	Request to send	Output
4	CS(CTS)	Clear to send	Input
5	SG(0V)	Signal ground	-
6	FG	Frame ground	_

Built-in RS-485 Port (2-wire) for S□□-type CPU Units

RS-485 Terminal Block




Pin	Abbr.	Signal Name	Signal direction
1	A-	Send/Receive data -	-
2	B+	Send/Receive data +	-
3	FG	Frame ground	-

DIP Switch for Terminating Resistance Settings

	Setting						
ONû	ON	OFF					
	OFF	OFF	Terminating resistance selection Resistance value: 220 Ω typical				

CP1W-CIF01 RS-232C Option Board




RS-232C Connector




Pin	Abbr.	Signal	Signal direction
1	FG	Frame ground	-
2	SD(TXD)	Send data	Output
3	RD(RXD)	Receive data	Input
4	RS(RTS)	Request to send	Output
5	CS(CTS)	Clear to send	Input
6	5V	Power	-
7	DR(DSR)	Data set ready	Input
8	ER(DTR)	Data terminal ready	Output
9	SG(0V)	Signal ground	-
Connector hood	FG	Frame ground	-

Note: 1. The NV3W-M□20L-V1 Programmable Terminal can be connected to pin 6 (+5V) on the RS-232C Option Board (CP1W-CIF01) mounted to the CPU Unit. Do not connect pin 6 to any other device.

CP1W-CIF11/CIF12-V1 RS-422A/485 Option Board



RS-422A/485 Terminal Block




DIP Switch for Operation Settings

CP1W-CIF11		CP1W-CIF12-	CP1W-CIF12-V1		Co#in#			
	Pin		Pin		Setting			
	1		1	ON	ON (both ends)	Terminating resistance selection		
	1	SW1		OFF	OFF	Resistance value: 220Ω typical		
	2	OZ	2	ON	2-wire connections	2 wire or 4 wire collection std		
SW 2	2		2	OFF	4-wire connections	2-wire or 4-wire selection *1		
	3	- 0 ω 4	3	ON	2-wire connections	2-wire or 4-wire selection *1		
0 Z	3			OFF	4-wire connections	2-wire of 4-wire selection *1		
	4		4	-	-	Not used.		
- 2 8 4 8 8 		5 SW2	1	ON	RS control enabled			
6	5			OFF	RS control disabled (Data always received.)	RS control selection for RD *2		
		6 - 2	2 z	ON	RS control enabled			
	6			OFF	RS control disabled (Data always sent.)	RS control selection for SD *3		

- *1. Set both pins 2 and 3 to either ON (2-wire) or OFF (4-wire).
- *2. To disable the echo-back function, set pin 5 to ON (RS control enabled).
- ***3.** When connecting to a device on the N side in a 1: N connection with the 4-wire method, set pin 6 to ON (RS control enabled). Also, when connecting by the 2-wire method, set pin 6 to ON (RS control enabled).

CP2W-CIFD1 RS-232C&RS-232C Option Board



RS-232C&RS-232C terminal block

RS-232C&RS-232C Terminal Block




Port	Pin	Abbr.	Signal Name	Signal direction
PORT□ -	1	SD(TXD)	Send data	Output
	2	RD(RXD)	Receive data	Input
	3	SG(0V)	Signal ground	
	4	FG	Frame ground	
	5	SD(TXD)	Send data	Output
DODT□ (EV)	6	RD(RXD)	Receive data	Input
PORT□ (EX)	7	SG(0V)	Signal ground	
	8	FG	Frame ground	

Note: 1. CP2W-CIFD1 can only be mounted on option slot 1.

PORT□ is supported by serial port 1 and PORT□ (EX) is supported by serial port 1(EX).

CP2W-CIFD2 RS-232C&RS-485 Option Board



RS-232C&RS-485 Terminal Block




Port	Pin	Abbr.	Signal Name	Signal direction
	1	SD(TXD)	Send data	Output
DODT	2	RD(RXD)	Receive data	Input
PORT□	3	SG(0V)	Signal ground	
	4	FG	Frame ground	
	5	A-	Send/Receive data -	Output
PORT□ (EX)	6	B+	Send/Receive data +	Input
	7	FG	Frame ground	
	8	NC	NC	

Note: CP2W-CIFD2 can only be mounted on option slot 1.
PORT□ is supported by serial port 1 and PORT□ (EX) is supported by serial port 1(EX).

DIP switch for terminating resistance settings

Setting						
RS-485 TERM	ON	ON (both ends)	Terminating resistance selection			
ON TO THE STATE OF	OFF	OFF	Resistance value: 220Ω typical			

CP2W-CIFD3 RS-485&RS-485 Option Board



RS-485&RS-485 Terminal Block



Port	Pin	Abbr.	Signal Name	Signal direction
	1	A-	Send/Receive data -	Output
DORT□	2	B+	Send/Receive data +	Input
PORT□	3	FG	Frame ground	
	4	NC	NC	
	5	A-	Send/Receive data -	Output
DODT□ (EV)	6	B+	Send/Receive data +	Input
PORT□ (EX)	7	FG	Frame ground	
	8	NC	NC	

Note: 1. CP2W-CIFD3 can only be mounted on option slot 1.


PORT□ is supported by serial port 1 and PORT□ (EX) is supported by serial port 1(EX).

DIP switch for terminating resistance settings

Pin		Setting			
DC_40E	1	ON	ON (both ends)	Terminating resistance selection	
RS-485 TERM	'	OFF	OFF	Resistance value: 220Ω typical	
ON ON	2			Not used.	
				Not used.	
PORTION NO.	4		Terminating resistance selection		
	4	OFF	OFF	Resistance value: 220Ω typical	

Analog Option Board

N□□-type CPU Units



Note: 1. Maximum one Analog Option Board can be mounted on an N□□-type CPU Unit.

If two Analog Option Boards are mounted, an option board error will occur and both Analog Option Boards do not work.

Analog Option Board

Analog option board units are non-isolated analog units which allow you to easily realize analog input/output function for CP2E N□□-type CPU Unit.

Analog Option Board		Voltage Input 0V~10V (Resolution: 1/4000)	Current Input 0mA~20mA (Resolution: 1/2000)	Voltage Output 0V~10V (Resolution: 1/4000)
Analog I/O Option Board	CP1W-MAB221	2CH		2CH
Analog Input Option Board	CP1W-ADB21	2CH		
Analog Output Option Board	CP1W-DAB21V			2CH

Specifications of Analog Option Board CP1W-ADB21

Item -		Specifi	cations	
iteiii		Voltage Input	Current Input	
Input signal range		0 to 10 V	0 to 20 mA	
Max. rated in	nput	0 to 15 V	0 to 30 mA	
External inpu	ıt impedance	200 k $Ω$ min.	Approx. 250 Ω	
Resolution		1/4000 (full scale)	1/2000 (full scale)	
	25°C	±0.5% (full scale)	±0.6% (full scale)	
Overall accuracy	0 to 60°C	±1.0% (full scale)	±1.2% (full scale)	
uoouiuoy	-20 to 0°C	±1.3% (full scale)	±1.5% (full scale)	
A/D convers	ion data	0000 to 0FA0 Hex	0000 to 07D0 Hex	
Averaging function		None		
Isolation method		No isolation between analog I/O terminals and internal circuits.		
Current cons	sumption	5 VDC: 20 mA max.		

CP1W-DAB21V

Item		Specifications		
		Voltage Output	Current Output	
Output signa	al range	0 to 10 V		
External output allowable load resistance		2 kΩ min.		
External output impedance		0.5 Ω max.		
Resolution		1/4000 (full scale)		
_	25°C	±0.5% (full scale)		
Overall accuracy	0 to 60°C	±1.0% (full scale)		
accuracy	-20 to 0°C	±1.3% (full scale)		
Set data (D/A conversion)		0000 to 0FA0 Hex		
Isolation method		No isolation between analog I/O terminals and internal circuits.		
Current consumption		5 VDC: 60 mA max.		

CP1W-MAB221

lta ma	Item -		Specifications		
item			Voltage I/O	Current I/O	
Input signal range		0 to 10 V	0 to 20 mA		
	Max. rated inp	ut	0 to 15 V	0 to 30 mA	
	External input	impedance	200 kΩ min.	Approx. 250 Ω	
	Resolution		1/4000 (full scale)	1/2000 (full scale)	
Analog Input Section		25°C	±0.5% (full scale)	±0.6% (full scale)	
	Overall accuracy	0 to 60°C	±1.0% (full scale)	±1.2% (full scale)	
	uccuracy	-20 to 0°C	±1.3% (full scale)	±1.5% (full scale)	
	A/D conversion data		0000 to 0FA0 Hex	0000 to 07D0 Hex	
	Averaging function		None		
	Output signal	range	0 to 10 VDC		
	External output		2 kΩ min.		
	External output impedance		0.5 Ω max.		
Analog Output Section	Resolution		1/4000 (full scale)		
	_	25°C	±0.5% (full scale)		
	Overall accuracy	0 to 60°C	±1.0% (full scale)		
	2300100	-20 to 0°C	±1.3% (full scale)		
	Set data (D/A conversion)		0000 to 0FA0 Hex		
Isolation method		No isolation between analog I/O terminals and internal circuits.			
Current consumption		5 VDC: 80 mA max.			

Analog Option Board Refresh Time (Typical values)

Analas Onitan Board	Cycle time (ms)				
Analog Opiton Board	1 ms	10 ms	20 ms		
CP1W-ADB21	16~40	20~60	20~100		
CP1W-DAB21V	9~37	26~58	46~86		
CP1W-MAB221(AD)	14~62	18~109	20~160		
CP1W-MAB221(DA)	9~53	26~102	46~150		


Specifications of Expansion I/O Units and Expansion Units

Expandable CPU Units

- Expansion I/O Units and Expansion Units cannot be connected to E14/20 or N14/20 CPU Units.
- A total of up to three Expansion I/O Units and Expansion Units can be connected to an E30/40/60, S30/40/60 or N30/40/60 CPU Unit.

CP2E-E14/20 or N14/20 CPU Unit






CP-series Expansion Units and Expansion I/O Units cannot be connected.

CP2E-E30/40/60, S30/40/60 or N30/40/60 CPU Unit

A total of up to three CP-series Expansion I/O Units and Expansion Units can be connected.



Connection Methods

Connection cables for the Expansion I/O Units and Expansion Units are used to connect the Units. The length can be extended by using a CP1W-CN811 I/O Connecting Cable (length: 800 mm).

Maximum Number of I/O Points for an Expansion I/O Unit or Expansion Unit

CPU Unit		Built-in I/O on C	PU Unit	Total number of Expansion I/O Units and Expansion Units that can be connected	Number of inputs: 24 Number of outputs: 16 Total number of I/O points when three CP1W-40ED□ Expansion I/O Units are connected		
	Total	Number of inputs	Number of outputs	can be connected	Total	Number of inputs	Number of outputs
CP2E-□14D□-□	14	8	6	Not possible.	14	8	6
CP2E-□20D□-□	20	12	8	Not possible.	20	12	8
CP2E-□30D□-□	30	18	12		150	90	60
CP2E-□40D□-□	40	24	16	3 Units maximum	160	96	64
CP2E-□60D□-□	60	36	24		180	108	72

Specifications of Expansion I/O Units

Input Specifications (CP1W-8ED/20EDR1/20EDT/20EDT1/40EDR/40EDT/40EDT1)

Item	Specification
Input voltage	24 VDC, +10% / -15%
Input impedance	4.7 kΩ
Input current	5 mA typical
ON voltage / current	14.4 VDC min. / 3mA min.
OFF voltage / current	5.0 VDC max. / 1mA max.
ON response time	1 ms max. *1
OFF response time	1 ms max. *1
Circuit configuration	Input indicator Insolation circuits COMI


Note: 1. Do not apply voltage in excess of the rated voltage to the input terminal.

Output Specifications Relay Outputs (CP1W-8ER/16ER/20EDR1/32ER/40EDR)

Item			Specification	
Max. switching capacity			2 A, 250 VAC (cos = 1), 2 A, 24 VDC (4 A/common)	
Min. switching capa	city		10 mA, 5 VDC	
	Flootrical	Resistive load	150,000 operations (24 VDC)	
Service life of relay	Electrical	Inductive load	100,000 operations (240 VAC, cosφ = 0.4)	
	Mechanical		20,000,000 operations	
ON response time			15 ms max.	
OFF response time			15 ms max.	
Circuit configuration			Output indicator Output indic	

Note: 1. Estimating the Service Life of Relays


The service life of output contacts is as shown in the following diagram.




Switching frequency: 1,800 operations/hour

^{*1.} The response time is the delay caused by hardware. The delay set in the PLC Setup (0 to 32 ms, default: 8 ms) must be added to this value. For the CP1W-40EDR/EDT/EDT1, a fixed value of 16 ms must be added.


2. Restrictions of CP1W-16ER/32ER
Limit the output load current to satisfy the following derating curve.



CP1W-32ER's maximum number of simultaneously ON output points is 24 (75%). Relation between Number of ON Outputs and Ambient Temperature (CP1W-32ER)



- 4. According to the ambient temperature, there are restrictions on power supply voltage and output load current for the CPU Units connected with the Expansion I/O Units (CP1W-8ER/16ER/20EDR1/32ER/40EDR). Use the PLC in the range of the power supply voltage and output load current as show below.
 - The ambient temperature is restricted for the DC power supply CPU Units.
 Derating curve of the output load current for Expansion I/O Units (CP1W-8ER/16ER/20EDR1/32ER/40EDR).



Transistor Outputs (Sinking or Sourcing)


	Specification							
ltem	CP1W-40EDT CP1W-40EDT1	CP1W-32ET CP1W-32ET1	CP1W-20EDT CP1W-20EDT1	CP1W-16ET CP1W-16ET1	CP1W-8ET CP1W-8ET1			
Max. switching capacity	4.5 to 30 VDC 0.3 A/output	4.5 to 30 VDC 0.3 A/output	24 VDC +10%/-5% 0.3 A/output	4.5 to 30 VDC 0.3 A/output	4.5 to 30 VDC 0.3 A/output			
*1	0.9 A/common 3.6 A/Unit	0.9 A/common 7.2 A/Unit	0.9 A/common 1.8 A/Unit	0.9 A/common 3.6 A/Unit	0.9 A/common 1.8 A/Unit			
Leakage current	0.1 mA max.	0.1 mA max.	0.1 mA max.	0.1 mA max.	0.1 mA max.			
Residual voltage	1.5 V max.	1.5 V max.	1.5 V max.	1.5 V max.	1.5 V max.			
ON response time	0.1 ms max.	0.1 ms max.	0.1 ms.	0.1 ms max.	0.1 ms max.			
OFF response time	1 ms max. At 24 VDC +10%/ -5%, 5 to 300 mA	1 ms max. At 24 VDC +10%/ -5%, 5 to 300 mA 1 ms max. At 24 VDC +10%/ -5%, 5 to 300 mA		1 ms max. At 24 VDC +10%/ -5%, 5 to 300 mA	1 ms max. At 24 VDC +10%/ -5%, 5 to 300 mA			
Maximum number of simultaneously ON outputs	16 points (100% load)	24 points (100% load)	8 points (100% load)	16 points (100% load)	8 points (100% load)			
Fuse #2	1 fuse/common							
Circuit configuration	Sinkin Outpu	it indicator	Sourcing Output in	ndicator COM (+	÷)			

Internal circuits

24 VDC/4.5 to 30 VDC 24 VDC/4.5 to 30 VDC

*1. If the ambient temperature is maintained below 50°C, up to 0.9 A/common can be used.

Internal



***2.** The fuse cannot be replaced by the user. Replace the Unit if the fuse breaks due to an short-circuit or overcurrent. **Note: 1.** Do not connect a load to an output terminal or apply a voltage in excess of the maximum switching capacity.

Specifications of Expansion Units Analog Input Units

Model		CP1W	/-AD041	CP1W	/-AD042		
Item		Voltage input	Current input	Voltage input	Current input		
Number of analog inputs		4 inputs (4 words allocated)					
Input signal range		0 to 5 V, 1 to 5 V, 0 to 10 V, or –10 to 10 V	0 to 20 mA or 4 to 20 mA	0 to 5 V, 1 to 5 V, 0 to 10 V, or -10 to 10 V	0 to 20 mA or 4 to 20 mA		
Max. rated input		±15 V	±30 mA	±15 V	±30 mA		
External input impedance)	1 MΩ min.	Approx. 250 Ω	1 MΩ min.	Approx. 250 Ω		
Resolution		1/6000 (full scale)		1/12000 (full scale)			
	25°C	0.3% full scale	0.4% full scale	0.2% full scale	0.3% full scale		
Overell conveni	0 to 55°C	0.6% full scale	0.8% full scale	0.5% full scale	0.7% full scale		
Overall accuracy	55 to 60°C	0.7% full scale	0.8% full scale	0.5% full scale	0.7% full scale		
	-20 to 0°C	0.8% full scale	1% full scale	0.7% full scale	0.9% full scale		
A/D conversion data		16-bit binary (4-digit hexadecimal) Full scale for –10 to 10 V: F448 to 0BB8 hex Full scale for other ranges: 0000 to 1770 hex		16-bit binary (4-digit hexadecimal) Full scale for –10 to 10 V: E890 to 1770 hex Full scale for other ranges: 0000 to 2EE0 hex			
Averaging function		Supported (Set in output words n+1 and n+2.)					
Open-circuit detection function		Supported					
Conversion time		2 ms/point (8 ms/all points)		1 ms/point (4 ms/all points)			
Isolation method		Photocoupler isolation between analog input terminals and internal circuits. No isolation between analog I/O signals.					
Current consumption		5 VDC: 100 mA max.; 24 VI	5 VDC: 100 mA max.; 24 VDC: 90 mA max. 5 VDC: 100 mA max.; 24 VDC: 50 mA max				

Analog Output Units

Model		CP1W-DA021	/CP1W-DA041	CP1\	W-DA042	
Item		Voltage output	Current output	Voltage output	Current output	
Number of analog outputs		CP1W-DA021: 2 outputs (2 CP1W-DA041: 4 outputs (4		4 outputs (4 words allocate	d)	
Output signal range		1 to 5 V, 0 to 10 V, or -10 to 10 V	0 to 20 mA or 4 to 20 mA	1 to 5 V, 0 to 10 V, or -10 to 10 V	0 to 20 mA or 4 to 20 mA	
External output allowable	load resistance	$2 \text{ k}\Omega$ min.	350 $Ω$ max.	$2 \text{ k}\Omega$ min.	350 $Ω$ max.	
External output impedance		0.5 Ω max.		0.5 Ω max.		
Resolution		1/6000 (full scale)		1/12000 (full scale)		
	25°C	0.4% full scale		0.3% full scale		
Overall accuracy	0 to 55°C	0.8% full scale		0.7% full scale		
	-20 to 0°C	1% full scale		0.9% full scale		
D/A conversion data		16-bit binary (4-digit hexadecimal) Full scale for –10 to 10 V: F448 to 0BB8 hex Full scale for other ranges: 0000 to 1770 hex		16-bit binary (4-digit hexadecimal) Full scale for –10 to 10 V: E890 to 1770 hex Full scale for other ranges: 0000 to 2EE0 hex		
Conversion time		CP1W-DA021: 2 ms/point (4 ms/all points) CP1W-DA041: 2 ms/point (8 ms/all points)		1 ms/point (4 ms/all points)		
Isolation method		Photocoupler isolation between analog output terminals and internal circuits. No isolation between analog I/O signal				
Current consumption			A max.; 24 VDC: 95 mA max. A max.; 24 VDC: 124 mA max.			

Analog I/O Units

Model			CP1W-MAD42	/CP1W-MAD44	CP1W-	-MAD11	
Item			Voltage I/O	Current I/O	Voltage I/O	Current I/O	
	Number of inp	uts	4 inputs (4 words allocated)		2 inputs (2 words allocated)		
	Input signal ra	nge	0 to 5 V, 1 to 5 V, 0 to 10 V, or –10 to 10 V	0 to 20 mA or 4 to 20 mA	0 to 5 V, 1 to 5 V, 0 to 10 V, or –10 to 10 V	0 to 20 mA or 4 to 20 mA	
	Max. rated inpu	ut	±15 V	±30 mA	±15 V	±30 mA	
	External input	impedance	1 MΩ min.	Approx. 250 Ω	1 MΩ min.	Approx. 250 Ω	
	Resolution		1/12000 (full scale)		1/6000 (full scale)		
Analog Input	_	25°C	0.2% full scale	0.3% full scale	0.3% full scale	0.4% full scale	
Section	Overall accuracy	0 to 55°C	0.5% full scale	0.7% full scale	0.6% full scale	0.8% full scale	
	accuracy	-20 to 0°C	0.7% full scale	0.9% full scale	0.8% full scale	1% full scale	
	A/D conversion	n data	16-bit binary (4-digit hexadecimal) Full scale for –10 to 10 V: E890 to 1770 hex Full scale for other ranges: 0000 to 2EE0 hex		16-bit binary (4-digit hexade Full scale for –10 to 10 V: F Full scale for other ranges:	448 to 0BB8 hex	
	Averaging fund	ction	Supported		Supported (Settable for indi	ividual inputs via DIP switch)	
	Open-circuit detection function		Supported				
	Number of outputs		CP1W-MAD42: 2 outputs (2 words allocated) CP1W-MAD44: 4 outputs (4 words allocated)		1 output (1 word allocated)		
	Output signal range		1 to 5 V, 0 to 10 V, or -10 to 10 V	0 to 20 mA or 4 to 20 mA	1 to 5 V, 0 to 10 V, or -10 to 10 V	0 to 20 mA or 4 to 20 mA	
	Allowable external output load resistance		2 kΩ min.	350 Ω max.	1 kΩ min.	600 Ω max.	
Analog Output	External output impedance		0.5 Ω max.		0.5 Ω max.		
Section	Resolution		1/12000 (full scale)		1/6000 (full scale)		
		25°C	0.3% full scale		0.4% full scale		
	Overall accuracy	0 to 55°C	0.7% full scale		0.8% full scale		
	accuracy	-20 to 0°C	0.9% full scale		1% full scale		
	Set data (D/A conversion)		16-bit binary (4-digit hexadecimal) Full scale for –10 to 10 V: E890 to 1770 hex Full scale for other ranges: 0000 to 2EE0 hex		16-bit binary (4-digit hexadecimal) Full scale for -10 to 10 V: F448 to 0BB8 hex Full scale for other ranges: 0000 to 1770 hex		
Conversion time		CP1W-MAD42: 1 ms/point (6 ms/all points) CP1W-MAD44: 1 ms/point (8 ms/all points)		2 ms/point (6 ms/all points)			
Isolation metho	d		Photocoupler isolation between analog I/O terminals and No isolation between analog I/O signals.		I internal circuits.		
Current consumption			CP1W-MAD42: 5 VDC: 120 mA max., 24 VDC: 120 mA max. CP1W-MAD44: 5 VDC: 120 mA max., 24 VDC: 170 mA max.		5 VDC: 83 mA max., 24 VDC: 110 mA max.		

Temperature Sensors Units

Item		CP1W-TS001	CP1W-TS002	CP1W-TS101	CP1W-TS102	
		Thermocouples		Platinum resistance thermome	ter	
Temperature sensors		Switchable between K and J, bu inputs.	it same type must be used for all	Switchable between Pt100 and JPt100, but same type must be used for all inputs.		
Number of inputs 2 4 2		2	4			
Allocated inpu	ıt words	2	4 2 4		4	
	25°C	(The larger of ±0.5% of converte	ed value or ±2°C) ±1 digit max.	(The larger of ±0.5% of converted value or ±1°C) ±1 digit max.		
Accuracy	0 to 60°C	(The larger of ±1% of converted	l value or ±4°C) ±1 digit max.	(The larger of ±1% of converted value or ±2°C) ±1 digit max.		
	-20 to 0°C	(The larger of ±1.3% of converte	d value or ±5°C) ±1 digit max. * 1	(The larger of ±1.3% of converted value or ±3°C) ±1 digit max.		
Conversion tir	ne	250 ms for 2 or 4 input points				
Converted ten	perature data	16-bit binary data (4-digit hexac	lecimal)			
Isolation		Photocouplers between all temp	perature input signals			
Current consumption 5		5 VDC: 40 mA max., 24 VDC: 5	9 mA max.	5 VDC: 54 mA max., 24 VDC: 73 mA max.		

^{*1.} Accuracy for a K-type sensor at -100°C or less is ±4°C ±1 digit max.

The rotary switch is used to set the temperature range.

Setting	CP1W-TS001/TS002			CP1W-TS101/TS102			
	Input type	Range (°C)	Range (°F)	Input type	Range (°C)	Range (°F)	
0	0	V	-200 to 1,300	-300 to 2,300	Pt100	-200.0 to 650.0	-300.0 to 1,200.0
		K	0.0 to 500.0	0.0 to 900.0	JPt100	-200.0 to 650.0	-300.0 to 1,200.0
		1	-100 to 850	-100 to 1,500			
3	J	0.0 to 400.0	0.0 to 750.0		Cannot be set.		
4 to F			Cannot be set.				


Main Specifications

Item			CP1W-TS003
Townsustance			Thermocouples or analog input *1
Temperature s	sensors		Switchable between K and J, but same type must be used for all inputs.
Number of inp	outs		4
Allocated inpu	ıt words		4
Max. number	of Units		3
Thermocouple inputs			(The larger of ±0.5% of converted value or ±2°C) ±1 digit max. *2
	25°C	Analog voltage inputs	0.5% full scale
		Analog current inputs	0.6% full scale
		Thermocouple inputs	(The larger of ±1% of converted value or ±4°C) ±1 digit max. *3
Accuracy	0 to 60 °C	Analog voltage inputs	1.0% full scale
		Analog current inputs	1.2% full scale
		Thermocouple inputs	(The larger of ±1.3% of converted value or ±5°C) ±1 digit max. *3
	-20 to 0 °C	Analog voltage inputs	1.2% full scale
		Analog current inputs	1.5% full scale
Thermocouple inputs		Thermocouple inputs	K: -200.0 to 1300.0°C or -300.0 to 2300.0°F J: -100.0 to 850.0°C or -100.0 to 1500.0°F
Input signal ra	inge	Analog voltage inputs	0 to 10V/1 to 5V
		Analog current inputs	4 to 20mA
Resolution		Thermocouple inputs	0.1°C or 0.1°F
Resolution		Analog inputs	1/12000 (full scale)
Max. rated inp	+	Analog voltage inputs	±15V
wax. rateu iiip	ut	Analog current inputs	±30mA
External input	impedance	Analog voltage inputs	1 Μ Ω min.
External input	impedance	Analog current inputs	250Ω
Open-circuit o	letection function	1	Supported
Averaging fun	ction		Unsupported
Conversion ti	me		250 ms for 4 input points
Converted ten	nperature data		16-bit binary data (4-digit hexadecimal) 2-decimal-place mode is not supported
Converted AD	data		16-bit binary data (4-digit hexadecimal)
Isolation			Photocouplers between any two input signals
Current consu	ımption		5 VDC: 70 mA max., 24 VDC: 30 mA max.

- ***1.** Only last two channels can be used as analog input. ***2.** Accuracy for a K-type sensor at -100°C or less is ±4°C ±1 digit max.
- ***3.** Accuracy for a K-type sensor at -100°C or less is ±10°C ±1 digit max.

DIP Switch Settings

With the Temperature Sensor Unit's DIP switch, set the input type (temperature or analog input), the input thermocouple type (K or J) and the temperature unit (°C or °F).



SW	Setting					
1	Thermosouple type of temperature concer	ON	J			
ı	Thermocouple type of temperature sensor	OFF	K			
2	Tammaratura unit	ON	°F			
2	Temperature unit	OFF	°C			
3	NC		·			
4	Input type selection for the third input (Input 2)	ON	Analog input			
4	input type selection for the third input (input 2)	OFF	Thermocouple			
5	Input time colories for the fourth input (Input 2)	ON	Analog input			
5	Input type selection for the fourth input (Input 3)	OFF	Thermocouple			
6	Analog input signal range	ON	1 to 5V/4 to 20mA			
6	Analog input signal range	OFF	0 to 10V			

	Temperature input	Analog input		
Input type Range (°C)		Range (°F)	Input type	Range
K	-200.0 to 1300.0	-300.0 to 2300.0	Voltage	0 to 10V/1 to 5V
J	-100.0 to 850.0	-100.0 to 1500.0	Current	4 to 20mA

Main Specifications

Item		CP1W-TS004
Townsvotus con		Thermocouples
Temperature sen	SOFS	Switchable between K and J, but same type must be used for all inputs.
Number of inputs	3	12
Allocated input w	vords	2
Allocated output words		1
	25°C	(The larger of ±0.5% of converted value or ±2°C) ±1 digit max. * 1
Accuracy	0 to 60°C	(The larger of ±1% of converted value or ±4°C) ±1 digit max. *2
	-20 to 0°C	(The larger of ±1.3% of converted value or ±5°C) ±1 digit max. *2
Conversion time	·	500 ms for 12 input points
Converted temperature data		16-bit binary data (4-digit hexadecimal) 2-decimal-place mode is not supported
Isolation		Photocouplers between any two input signals
Current consump	otion	5 VDC: 80 mA max., 24 VDC: 50 mA max.

DIP Switch Settings

With the Temperature Sensor Unit's DIP switch, set the temperature unit and the temperature input range.




sw	Setting			
4	langet temp	ON	J	
1	Input type	OFF	K	
2	Temperature unit	ON	°F	
2		OFF	°C	


Temperature input						
Input type Range (°C) Range (
K	-200.0 to 1300.0	-300.0 to 2300.0				
J	-100.0 to 850.0	-100.0 to 1500.0				

^{* 1} Accuracy for a K-type sensor at -100°C or less is ±4°C ±1 digit max. * 2 Accuracy for a K-type sensor at -100°C or less is ±10°C ±1 digit max.


Dimensions (Unit: mm)


CPU Units with 14 or 20 I/O Points CP2E-N14/20D□-□







CP2E-E14/20D□-□







CPU Units with 30 I/O Points CP2E-N30D□-□






$CP2E-E30D\Box-\Box$, $CP2E-S30D\Box-\Box$







CPU Units with 40 I/O Points

CP2E-N40D□-□




CP2E-E40D□-□, **CP2E-S40D**□-□






CPU Units with 60 I/O Points


CP2E-N60D□-□




CP2E-E60D□-□, **CP2E-S60D**□-□





Expansion I/O Units and Expansion Units CP1W-8E□□





CP1W-40ED CP1W-32E CP1W-TS004





Comparison of specifications of CP2E and CP1E

Omanification		CP2E			CF	P1E	
Specifications	CP2E-N□□	CP2E-S□□	CP2E-E□□	CP1E-N□□	CP1E-N□□S□	CP1E-E□□ CP1E-E□□S	CP1E-NA20
Number of built-in I/O points	14/20/30/40/60	30/40/60	14/20/30/40/60	14/20/30/40/60	30/40/60	10/14/20/30/40/60	20
Total number of Expansion units	14/20 points None 30/40/60 points 3 u			14/20 points None 30/40/60 points 3 units			
Lineup Output/power supply type	Relay/AC Relay/DC Transistor (sinking)/AC Transistor (sinking)/DC Transistor (sourcing)/DC	Relay/AC Transistor (sinking)/DC Transistor (sourcing)/DC	• Relay/AC	Relay/AC Relay/DC Transistor (sinking)/AC Transistor (sourcing)/AC Transistor (sinking)/DC Transistor (sourcing)/DC	Relay/AC Transistor (sinking)/DC Transistor (sourcing)/DC	Relay/AC Only 10 points Relay/DC Transistor (sinking)/AC Transistor (sourcing)/AC Transistor (sinking)/DC Transistor (sinking)/DC Transistor (sourcing)/DC	Relay/AC Transistor (sinking)/DC Transistor (sourcing)/DC
Program capacity	10K steps	8K steps	4K steps	8K steps	8K steps	2K steps	8K steps
FB capacity	10K steps	8K steps	4K steps	None		1	II.
Function block steps		in function block de structured text (ST)	finitions:	None			
Overhead processing time	0.2 ms	0.15 ms	0.1 ms	0.4 ms			
Instruction execution times	LD 0.23 μs MOV 1.76 μs			LD 1.19 μs MOV 7.9 μs			
Data memory capacity	16K words	8K words	4K words	8K words	8K words	2K words	8K words
IO Memory backup		memory (Batteryles	ss backup)	Built-in SRAM (Ba	ttery backup)	1	T
Pulse outputs	N14/20: 2 outputs 100 kHz N30/40/60: 4 outputs 100 kHz (Linear interpolation possible)	2 outputs 100 kHz	None	2 outputs 100kHz	2 outputs 100kHz	None	2 outputs 100kHz
High-speed counters (Differential Phase)	N14/20: 2 counters (50 kHz, 5 kHz) N30/40/60: 2 counters (50 kHz x2)	2 counters (50 kHz, 5 kHz)		2 counters (50 kHz	z,5 kHz)	2 counters (5 kHz x2)	2 counters (50 kHz, 5 kHz)
Quick-response Interrupt inputs	8 inputs (6 inputs only for 14 points)	6 inputs		6 inputs (4 inputs only for 10 points)			
Ethernet port	Included N14/20: 1 port N30/40/60: 2 port	None	None	None N30/40/60 only: 1 port (CP1W-CIF41 use)	None	None	1 port (CP1W-CIF41 use)
USB port	None	Included	Included	Included			
Serial port	N14/20: Max 2 port (Option boards use) N30/40/60: Max 3 port (Option boards use)	2 port RS-232C RS-485	1 port RS-232C	N14/20: 1 port RS-232C N30/40/60: Max 2 port RS-232C Option board	1 port RS-232C N30/40/60 S1 Type only: Max 2 port RS-232C RS-485	None	Max 2 port RS-232C Option board
Serial communication protocols	Host Link 1: N NT Link (1: N) No-protocol mode Serial PLC Link (master, slave) Modbus-RTU easy master Modbus-RTU Slave			Host Link 1: N NT Link (1: N) No-protocol mode Serial PLC Link (master, slave) Modbus-RTU easy master			
Option Boards	N14/20: 1 unit N30/40/60: 2 units	None	None	N14/20: None N30/40/60: 1 unit	None	None	1 unit
Clock function	Yes	Yes	None	Yes	Yes	None	Yes
Corresponding battery	CP2W-BAT02 (for clock function)		None	CP1W-BAT01 (for clock function,	IO memory backup)	None	CP1W-BAT01
Built-in analog	None			None			Analog input 2channels Analog output 1channel
	None	None	None	Yes	None	EDD: Yes	Yes
Analog adjusters						E□□S: None	

Easy to convert CP1E code into CP2E code

Uploaded CP1E code can be converted into CP2E code with just one click.



Cx-One Ver 4.51 or higher Cp-programmer Ver 9.72 or higher

Examples of replacement of CP1E with CP2E

CP1E-E□□/E□□S	CP2E-E□□
CP1E-E10D□-□	CP2E-E14DR-A or others
CP1E-E14SDR-A/E14DR-A	CP2E-E14DR-A
CP1E-E20SDR-A/E20DR-A	CP2E-E20DR-A
CP1E-E30SDR-A/E30DR-A	CP2E-E30DR-A
CP1E-E40SDR-A/E40DR-A	CP2E-E40DR-A
CP1E-E60SDR-A	CP2E-E60DR-A

CP1E-N□□S	CP2E-S□□
CP1E-N30SD□-□/N30S1D□-□	CP2E-S30D□-□
CP1E-N40SD□-□/N40S1D□-□	CP2E-S40D□-□
CP1E-N60SD□-□/N60S1D□-□	CP2E-S60D□-□

CP1E-N□□	CP2E-S□□ * 1	CP2E-N□□ * 1	
CP1E-N14D□-□	-	CP2E-N14D□-□	
CP1E-N20D□-□	-	CP2E-N20D□-□	
CP1E-N30D□-□	CP2E-S30D□-□	CP2E-N30D□-□	
CP1E-N40D□-□	CP2E-S40D□-□	CP2E-N40D□-□	
CP1E-N60D□-□	CP2E-S60D□-□	CP2E-N60D□-□	
CP1E-NA20□-□	-	CP2E-N30D□-□ + CP1W-MAB221 or others	

^{*1.} When the AC powered N30/40/60 CPU Unit with relay outputs, or the DC powered N30/40/60 CPU Unit with transistor outputs is used without an option board or with the CP1W-CIF11 Option Board, it is recommended to replace with the CP2E-S□□. When any of the other CPU units is used with an option board, it is recommended to replace with the CP2E-N□□. For details, refer to the *Replacement Guide from CP1E to CP2E* (Cat. No. P150).

CP2E

Related Manuals

Manual name	Cat. No.	Model numbers	Application	Contents
SYSMAC CP Series CP2E CPU Unit Hardware User's Manual	W613	CP2E-E DD - CP2E-N	To learn the hardware specifications of the CP2E PLCs	Describes the following information for CP2E PLCs. Overview and features Basic system configuration Part names and functions Installation and settings Troubleshooting
SYSMAC CP Series CP2E CPU Unit Software User's Manual	W614	CP2E-E D D - CP2E-S D D - CP2E-N D - CP2E-N D - CP2E-N D D D - CP2E-N	To learn the software specifications of the CP2E PLCs	Describes the following information for CP2E PLCs. CPU Unit operation Internal memory Programming Settings CPU Unit built-in functions Interrupts High-speed counter inputs Pulse outputs Serial communications Ethernet Other functions
SYSMAC CP Series CP1E/CP2E CPU Unit Instructions Reference Manual	W483	CP1E-E DD - CP1E-N DD - CP1E-N DD - CP1E-N C	To learn programming instructions in detail	Describes each programming instruction in detail.
CS/CJ/CP/NSJ Series Communications Commands Reference Manual	W342	CS1G/H-CPU	To learn communications commands for CS/CJ/CP/NSJ-series Controllers in detail	Describes 1) C-mode commands and 2) FINS commands in detail. Read this manual for details on C-mode and FINS commands addressed to CPU Units.
CX-One FA Integrated Tool Package Setup Manual	W463		To install the software provided in the CX-One	Describes the overview of the CX-One FA Integrated Tool Package, and how to install and uninstall the CX-One.
CX-Programmer Operation Manual	W446		To learn the operation procedures	
CX-Programmer Operation Manual (Function Blocks/ Structured Text)	W447	CXONE-AL□□D-V4	for the CX-Programmer, the Programming Device for Windows computers	Describes the operation procedures for the CX-Programmer.
CX-Simulator Operation Manual	W366		To learn the operation procedures for the CX-Simulator, the Simulation Device for Windows computers	Describes the operation procedures for the CX-Simulator.
CX-Integrator Operation Manual	W464		To set up and monitor networks	Describes the operation procedures for the CX-Integrator.

Microsoft, Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and other countries. Other company names and product names in this document are the trademarks or registered trademarks of their respective companies. The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2019-2024 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_2_7

Cat. No. P145-E1-06 0924 (0919)