

Discontinuation Notice of Light Curtains F3EM2 & F3ET2 Series.**Product Discontinuation**

Measuring Light Curtains

**Model F3EM2
Model F3ET2****Recommended Replacement**

Safety Light Curtains

**Model F3SG-SR/PG
Model F3SG-SR/PG****[Final order entry date]**

The end of October, 2022

[Date of The Last Shipping]

The end of December, 2022

[Difference from discontinued product]

Recommended replacement Model	Body Color	Dimensions	Wire connection	Mounting Dimensions	Characteristics	Operation ratings	Operation methods
F3EM2 & F3ET2	--	--	--	--	--	--	--

** : Compatible

* : The change is a little/Almost compatible

-- : Not compatible

- : No corresponding specification

***IMPORTANT:** The recommended replacement must be tested as it is not a direct alternative. There are major differences:

IO-Link system : Safety light curtain + I-Tap + IO-link master + controller**Output** : IO-Link**Resolution** : > 14mm**Response time** : > 700-900ms depends on the controller**[Product Discontinuation and recommended replacement]**

Product discontinuation	Recommended replacement
F3ET2-005-150	No recommended replacement
F3ET2-018-150	F3SG-2SRB0160-14 + F39-SGIT-IL3
F3ET2-005-300	No recommended replacement
F3ET2-018-300	F3SG-2SRB0320-14 + F39-SGIT-IL3
F3ET2-005-450	No recommended replacement
F3ET2-018-450	F3SG-2SRB0480-14 + F39-SGIT-IL3
F3ET2-005-600	No recommended replacement
F3ET2-018-600	F3SG-2SRB0640-14 + F39-SGIT-IL3

Product discontinuation	Recommended replacement
F3ET2-005-900	No recommended replacement
F3ET2-018-900	F3SG-2SRB1000-14 + F39-SGIT-IL3
F3ET2-005-1200	No recommended replacement
F3ET2-018-1200	F3SG-2SRB1200-14 + F39-SGIT-IL3
F3ET2-005-1500	No recommended replacement
F3ET2-018-1500	F3SG-2SRB1600-14 + F39-SGIT-IL3
F3ET2-005-1800	No recommended replacement
F3ET2-018-1800	F3SG-2SRB1800-14 + F39-SGIT-IL3
F3ET2-018-2100	F3SG-2SRB2000-14 + F39-SGIT-IL3
F3ET2-007-100	No recommended replacement
F3ET2-005-200	No recommended replacement
F3ET2-007-100-T	No recommended replacement
F3ET2-018-750	F3SG-2SRB0800-14 + F39-SGIT-IL3
F3EM2-005-150-AV	No recommended replacement
F3EM2-018-150-AV	F3SG-2SRB0160-14 + F39-SGIT-IL3
F3EM2-005-300-AV	No recommended replacement
F3EM2-018-300-AV	F3SG-2SRB0320-14 + F39-SGIT-IL3
F3EM2-005-450-AV	No recommended replacement
F3EM2-018-450-AV	F3SG-2SRB0480-14 + F39-SGIT-IL3
F3EM2-005-600-AV	No recommended replacement
F3EM2-018-600-AV	F3SG-2SRB0640-14 + F39-SGIT-IL3
F3EM2-005-900-AV	No recommended replacement
F3EM2-018-900-AV	F3SG-2SRB1000-14 + F39-SGIT-IL3
F3EM2-005-1200-AV	No recommended replacement
F3EM2-018-1200-AV	F3SG-2SRB1200-14 + F39-SGIT-IL3
F3EM2-005-1500-AV	No recommended replacement
F3EM2-018-1500-AV	F3SG-2SRB1600-14 + F39-SGIT-IL3
F3EM2-005-1800-AV	No recommended replacement
F3EM2-018-1800-AV	F3SG-2SRB1800-14 + F39-SGIT-IL3
F3EM2-018-2100-AV	F3SG-2SRB2000-14 + F39-SGIT-IL3
F3EM2-005-150	No recommended replacement
F3EM2-018-150	F3SG-2SRB0160-14 + F39-SGIT-IL3
F3EM2-005-300	No recommended replacement
F3EM2-018-300	F3SG-2SRB0320-14 + F39-SGIT-IL3
F3EM2-005-450	No recommended replacement
F3EM2-018-450	F3SG-2SRB0480-14 + F39-SGIT-IL3
F3EM2-005-600	No recommended replacement
F3EM2-018-600	F3SG-2SRB0640-14 + F39-SGIT-IL3
F3EM2-005-900	No recommended replacement
F3EM2-018-900	F3SG-2SRB1000-14 + F39-SGIT-IL3
F3EM2-005-1200	No recommended replacement
F3EM2-018-1200	F3SG-2SRB1200-14 + F39-SGIT-IL3
F3EM2-005-1500	No recommended replacement
F3EM2-018-1500	F3SG-2SRB1600-14 + F39-SGIT-IL3
F3EM2-005-1800	No recommended replacement
F3EM2-018-1800	F3SG-2SRB1800-14 + F39-SGIT-IL3
F3EM2-018-2100	F3SG-2SRB2000-14 + F39-SGIT-IL3
F3EM2-018-1650-485	F3SG-2SRB1600-14 + F39-SGIT-IL3
F3EM2-018-1200-485	F3SG-2SRB1200-14 + F39-SGIT-IL3

Product discontinuation	Recommended replacement
F3EM2-018-1650-AV	F3SG-2SRB1600-14 + F39-SGIT-IL3
F3EM2-018-2100-485	F3SG-2SRB2000-14 + F39-SGIT-IL3
F3EM2-005-100-AV	No recommended replacement
F3EM2-018-2400-485	No recommended replacement
F3EM2-018-2550-485	No recommended replacement
F3EM2-005-600-485	No recommended replacement
F3EM2-018-3000-485	No recommended replacement
F3EM2-018-2250-485	No recommended replacement
F3EM2-018-2700-485	No recommended replacement
F3EM2-005-1500-485	No recommended replacement
F3EM2-007-1000-485	No recommended replacement
F3EM2-018-1800-485	F3SG-2SRB1800-14 + F39-SGIT-IL3
F3EM2-018-450-485	F3SG-2SRB0480-14 + F39-SGIT-IL3
F3EM2-018-3600-485	No recommended replacement
F3EM2-018-4050-485	No recommended replacement
F3EM2-007-1050-485	No recommended replacement
F3EM2-018-1050-485	F3SG-2SRB1000-14 + F39-SGIT-IL3
F3EM2-018-1950-485	F3SG-2SRB2000-14 + F39-SGIT-IL3
F3EM2-018-2250-AV	No recommended replacement
F3EM2-005-900-485	No recommended replacement
F3EM2-005-1800-485	No recommended replacement
F3EM2-018-1500-485	F3SG-2SRB1600-14 + F39-SGIT-IL3
F3EM2-018-300-485	F3SG-2SRB0320-14 + F39-SGIT-IL3
F3EM2-018-900-485	F3SG-2SRB1000-14 + F39-SGIT-IL3
F3EM2-005-150-485	No recommended replacement
F3EM2-018-600-485	F3SG-2SRB0640-14 + F39-SGIT-IL3
F3EM2-018-3300-485	No recommended replacement
F3EM2-018-3150	No recommended replacement
F3EM2-018-2250	No recommended replacement
F3EM2-018-2400-485-1	No recommended replacement
F3EM2-007-1350	No recommended replacement
F3EM2-018-750-AV	F3SG-2SRB0800-14 + F39-SGIT-IL3
F3EM2-005-1200-485	No recommended replacement
F3EM2-007-2400-485	No recommended replacement
F3EM2-005-300-485	No recommended replacement
F3EM2-007-650-C	No recommended replacement
F3EM2-018-3450-485	No recommended replacement
F3ET2-005-150	No recommended replacement
F3ET2-018-150	F3SG-2SRB0160-14 + F39-SGIT-IL3
F3ET2-005-300	No recommended replacement
F3ET2-018-300	F3SG-2SRB0320-14 + F39-SGIT-IL3

Specifications and prices in this product news are as of the issue date and are subject to change without notice. Only main changes in specifications are described in this document. Please be sure to read the relevant catalogs, datasheets, product specifications, instructions, and manuals for precautions and necessary information when using products.